



ELECTRONICS, INC.  
44 FARRAND STREET  
BLOOMFIELD, NJ 07003  
(973) 748-5089  
<http://www.nteinc.com>

## NTE74LS54 Integrated Circuit TTL – 4-Wide AND/OR Invert Gate

### **Description:**

The NTE74LS54 is a 4-wide AND/OR invert gate in a 14-Lead plastic DIP type package that contains one 4-wide AND/OR Invert gate that performs the Boolean function  $Y = \overline{AB} + CDE + FGH + IJ$ .

### **Absolute Maximum Ratings:** (Note 1)

Supply Voltage, $V_{CC}$ .....	7V
Input Voltage .....	7V
Operating Temperature Range, $T_A$ .....	0°C to +70°C
Storage Temperature Range, $T_{stg}$ .....	-65°C to +150°C

Note 1. Voltage values are with respect to network ground terminal..

### **Recommended Operating Conditions:**

Parameter	Symbol	Min	Typ	Max	Unit
Supply Voltage	$V_{CC}$	4.75	5.0	5.25	V
High-Level Input Voltage	$V_{IH}$	2	–	–	V
Low-Level Input Voltage	$V_{IL}$	–	–	0.8	V
High-Level Output Current	$I_{OH}$	–	–	-0.4	mA
Low-Level Output Current	$I_{OL}$	–	–	8	mA
Operating Temperature Range	$T_A$	0	–	+70	°C

### **Electrical Characteristics:** (Note 2, Note 3)

Parameter	Symbol	Test Conditions		Min	Typ	Max	Unit
Input Clamp Voltage	$V_{IK}$	$V_{CC} = \text{MIN}$ , $I_I = -18\text{mA}$	–	–	-1.5	V	
High Level Output Voltage	$V_{OH}$	$V_{CC} = \text{MIN}$ , $V_{IL} = \text{MAX}$ , $I_{OH} = -0.4\text{mA}$	2.7	3.4	–	V	
Low Level Output Voltage	$V_{OL}$	$V_{CC} = \text{MIN}$ , $V_{IH} = 2\text{V}$	$I_{OL} = 4\text{mA}$	–	0.25	0.4	V
			$I_{OL} = 8\text{mA}$	–	0.35	0.5	V
Input Current	$I_I$	$V_{CC} = \text{MAX}$ , $V_I = 7\text{V}$	–	–	0.1	mA	

Note 2. For conditions shown as MIN or MAX, use the appropriate value specified under "Recommended Operation Conditions".

Note 3. All typical values are at  $V_{CC} = 5\text{V}$ ,  $T_A = +25^\circ\text{C}$ .

### **Electrical Characteristics (Cont'd): (Note 2, Note 3)**

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
High Level Input Current	I <sub>IH</sub>	V <sub>CC</sub> = MAX, V <sub>I</sub> = 2.7V	-	-	20	μA
Low Level Input Current	I <sub>IL</sub>	V <sub>CC</sub> = MAX, V <sub>I</sub> = 0.4V	-	-	-0.4	mA
Short-Circuit Output Current	I <sub>IL</sub>	V <sub>CC</sub> = MAX, Note 4	-20	-	-100	mA
Supply Current	I <sub>CCH</sub>	V <sub>CC</sub> = MAX, V <sub>i</sub> = 0V	-	0.8	1.6	mA
	I <sub>CCL</sub>	V <sub>CC</sub> = MAX, Note 5	-	1	2	mA

Note 2. For conditions shown as MIN or MAX, use the appropriate value specified under "Recommended Operation Conditions".

Note 3. All typical values are at V<sub>CC</sub> = 5V, T<sub>A</sub> = +25°C.


Note 4. Not more than one output should be shorted at a time, and the duration of the short-circuit should not exceed one second.

Note 5. All inputs of one AND gate at 4.5V, all others at GND

### **Switching Characteristics: (V<sub>CC</sub> = 5V, T<sub>A</sub> = +25°C unless otherwise specified)**

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Propagation Delay Time (From Any Input to Y Output)	t <sub>PLH</sub>	R <sub>L</sub> = 2kΩ, C <sub>L</sub> = 15pF	-	12	20	ns
	t <sub>PHL</sub>		-	12.5	20	ns

**Logic Diagram**



### Pin Connection Diagram

