

Angular milling cutter 90°

For AP... indexable milling inserts 1604..

ATORN®


Application

For universal use in all materials.

Version

- Wear-resistant, nickel-plated version
- With internal cooling
- Clamping screw tightening torque (indexable insert) M4 = 5.2 Nm

Art. No.	16019 027
Cutting edge diameter	200 mm
Length	63 mm
Bore diameter	60 mm
max. ap	14.9 mm
Number of cutting edges	13 PCS
Suitable indexable insert no.	27, 28



EAN-Code

4050293113532