



Figure similar

OUTPUT CHOKE; PHASES:3; UN1(V):500; ITHMAX 1(A) / F1(HZ):72 /200; F TAKT(KHZ):4; I LN (A):64,8; LN(MH):0,22; UK(%):7; TA/ISOKL:40 /H; IP00; TYPE OF TERMINALS:FLAT-TYPE TERMINAL; EN61558-2-20 >CHOKE<

General technical data:

Product designation		output reactor
product brand name		SIDAC
Phase number		3
Type of voltage		AC
Operating voltage Rated value		
• maximum	V	500
Operating frequency Rated value		
• minimum	Hz	0
• maximum	Hz	200
Current		
• with AC		
— Rated value	A	64.8
— maximum	A	72
Inductivity Rated value	H	0.00022
Active power loss of the coil	W	107.9
Active power loss of the iron core	W	38.7
Clock frequency		
• Rated value	Hz	4 000
• maximum	Hz	8 000

Mechanical data:

Type of electrical connection for main current circuit		flat connector
Width	m	0.22
Height	m	0.21
Depth	m	0.13

Ambient conditions:

Thermal class acc. to IEC 60085		H
Ambient temperature Rated value	°C	40
Protection class IP		IP00

Certificates/ approvals:

General Product Approval



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4EU24520EF004BA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4EU24520EF004BA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4EU24520EF004BA0&lang=en

last modified:

15.01.2015