

XPA clamping mandrels

for components with through-bores

Application:

For clamping workpieces.

Execution:

- Made from steel
- 5-side machining possible
- Multiple clamping possible

Advantage:

- The diameter of the fastening flange is concentric to the clamping diameter, thus ensuring excellent repeat accuracy
- Space-saving
- Easily machinable owing to structural steel design
- Easy to use



Art. no.	26221 105
Brand	IBT
Manufacturer Part Number	X38350
Distance	39.6 mm
Distance 2	27 mm
Grip height	31.8 mm
Min. clamping diameter	29.3 mm
Thickness	7.9 mm
Flange diameter	75.5 mm
Max. clamping diameter	51.5 mm
Suitable cheese-head screw DIN 912	M16
Tension force	44.5 kN
Reference circle diameter	63.9 mm
Length	22 mm
Gross Weight	0.797 kg
Product Group	278