


REV.	DATE	ECR NO.	DESCRIPTION
NC	09/22/02	XXXXXX	INITIAL RELEASE
A	02/28/14	2707	CORRECT BODY PLATING FROM GOLD TO NICKEL, UPDATE DRAWING FORMAT



1. IMPEDANCE: 50 OHM
2. FREQUENCY RANGE: 0-4 GHZ
3. DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS, MIN.
4. DURABILITY: 500 CYCLES MIN.
5. TEMPERATURE RANGE: -40°C TO +85°C

QTY	DESCRIPTION	MATERIAL	FINISH	DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex			
1	SHELL	BRASS	NICKEL	<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: <0.5 ± 0.05mm 0.5 - 6mm ± 0.10mm 6 - 30mm ± 0.20mm 30 - 120mm ± 0.30mm ANGLES ± 1° UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: <.020 ± 0.002" .020 - .236 = ± 0.004" .236 - 1.180 = ± 0.007" 1.180 - 4.724 = ± 0.012" ANGLES ± 1°</small>	DRAWN	M.ZHANG	02/28/14	SMA JACK TO TNC REVERSE POLARITY PLUG ADAPTER		
1	GASKET	SILICONE RUBBER	RED		CHECKED					
1	RETAINER RING	BRASS	NICKEL		ISSUED					
1	RING	DELTRIN	NATURAL		SHEET	1 OF 1				
1	WASHER	BRASS	NICKEL							
1	BODY	BRASS	NICKEL		CAD FILE	C:/CONNEX/242105RP.DWG		PART NO. 242105RP		
1	BODY	BRASS	NICKEL					DWG. NO. 242105RP.DWG		
1	INSULATOR	PTFE	NATURAL					REV.	SIZE	SCALE
1	CONTACT PIN	PHOSPHOR BRONZE	GOLD					A	A	NA