



Electrical Testing  
per Tusonix standard  
test plans and Mil-Std-202  
Test Methods.

**MARKETING SALES DRAWING**  
**DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING**  
**DIMENSIONS IN METRIC - [ ]**



NOTE:  
SUPPLIED WITH SILVER PLATED  
HEX NUT AND LOCKWASHER.

CAP. (pF)	WORKING VOLTAGE (WVdc)		CURRENT (Idc)	I.R. MIN. @ 100 VDC	D.W.V.	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD -220			
	85°C	125 °C				10 MHz	100 MHz	1 GHz	10 GHz
	1500	200	100	10 A	10 G Ω	400 VDC	5	45	65
2595	4	5							

REVISION RECORD	0	1	2	3	4	5	6	7	8	9
Original Release C.O.	WAS SK6644-031-S. L.E. 1-13-84	MIN CAP PF 1300 ADDED L.E. 8-16-84	DIMS & TOLS REV'D. RELEASED. LE 1-8-85	CURRENT UNIT "A" ADDED. L.E. 8-20-85	10 GHZ WAS 60. E.C. 7-14-92	RDN TO COMP FMT & ADDED METRIC. S.M. 01-21-02	20020121-1-01	20030414-3-01	--TOLERANCES-- Unless Otherwise Specified	Title <b>BUSHING STYLE EMI FILTER</b>
									DECIMAL ± .031 [0.79]	
									ANGLES ± / / /	Drawn S.M. 01-21-02 Scale 4X
										Approved T.C. 01-21-02
									A	4201-001
TUSONIX TUCSON, ARIZONA										