

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **1203410504**  
**Status:** **Active**  
**Overview:** Brad Industrial Ethernet Solutions  
**Description:** Micro-Change M12 to Standard RJ-45 CAT6A Double-Ended Cordset, 8 Poles, Male (Straight) to Male (Straight), 26 AWG, Shielded PUR Cable, 4.0m (13.12') Length

**Documents:**

[Drawing \(PDF\)](#)      [Packaging Specification PK-120341-140 \(PDF\)](#)  
[Product Specification PS-120341-140-001 \(PDF\)](#)      [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Cordsets
Series	<u>120341</u>
Connector End A	Micro-Change (M12)
Connector End B	RJ-45 (standard)
IP Rating	IP20, IP67
Material - Contact	Brass
Overview	<u>Brad Industrial Ethernet Solutions</u>
Performance Category	6A
Product Name	Micro-Change (M12) Cat6A
Protocol	N/A
Region	America, Asia, Europe
Type	Double Ended
UPC	887191128078

**Physical**

Cable Diameter	6.40mm (.252")
Cable Length	4.0m (13.12')
Color - Cable Jacket	Blue
Coupling Style	Threaded
Gender	Male-Male
Keyway	X-coded
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-40°C to +70°C
Wire Size AWG	26
Wire/Cable Type	Shielded PUR

**Electrical**


Current - Maximum per Contact	0.5A
Voltage - Maximum	48V

**Material Info**

Engineering Number	E26E06020M040
--------------------	---------------

**Reference - Drawing Numbers**

Packaging Specification	PK-120341-140
Product Specification	PS-120341-140-001
Sales Drawing	1203410500-000



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

120341 Series

**Mates With**

120341 Micro-Change CAT6A Receptacles

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**