



LED COVER FOR POSITION SWITCH PLASTIC  
3SE52, FOR HOUSING ACC. TO EN50047,31MM  
LEDS 24V DC YELLOW/GREEN TURQUOISE

Product designation	cover for enclosures EN 50047, plastic, turquoise, LEDs 24 V DC	
<b>General technical data:</b>		
Shock resistance	30g / 11 ms	
Vibration resistance	0.35 mm / 5g	
Protection class IP	IP65	
Explosion protection category for dust	none	
Explosion protection category for gas	none	
<b>Enclosure:</b>		
Design of the housing	block, narrow	
Coating of the enclosure	Other types	
<b>Drive Head:</b>		
Design of the operating mechanism	without	
<b>Communication/ Protocol:</b>		
Design of the interface	without	
<b>Ambient conditions:</b>		
<b>Ambient temperature</b>		
• during operation	°C	-25 ... +60
• during storage	°C	-40 ... +90
<b>Supply voltage:</b>		
<b>Type of voltage of the supply voltage</b>		
• of the optional LED indicator		DC
<b>Supply voltage</b>		

• of LED


V

24

### Installation/ mounting/ dimensions:

mounting position	any
Mounting type	screw fixing

### Certificates/ approvals:

General Product Approval	Declaration of Conformity	Test Certificates	other		
 CSA	 UL		 EG-Konf.	<a href="#">Special Test Certificate</a>	<a href="#">Confirmation</a>

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3SE52301AA00>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/3SE52301AA00/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=3SE52301AA00&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=3SE52301AA00&lang=en)



**last modified:**

16.03.2015