

For more Information
please call

1-800-Belden1



General Description:

Tinned copper conductor, PVC insulation.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	4	133x25	TC - Tinned Copper

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	.060

Overall Insulation

Overall Cable

Overall Nominal Diameter: 0.392 in.

Mechanical Characteristics (Overall)

Bulk Cable Weight: 193 lbs/1000 ft.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

UL Rating: 600 V, 105°C

UL Type: MTW or AWM 1015/1283

CSA Rating: 600 V, 105°C

CSA Type: TEW

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 07/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: VW-1

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

0.250

Max. Recommended Current:

Description	Current
Single conductor in free air @ 30C.	160 amps

Put Ups and Colors:

9904 Hook-up/Lead - UL AWM Style 1283 and 1015

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9904 001500	500 FT	101.500 LB	BROWN	C	#4 STR PVC BRN
9904 00250	50 FT	11.250 LB	RED	C	#4 STR PVC RED
9904 002500	500 FT	101.500 LB	RED	C	#4 STR PVC RED
9904 00750	50 FT	11.250 LB	VIOLET	C	#4 STR PVC VIO
9904 01050	50 FT	11.250 LB	BLACK	C	#4 STR PVC BLK
9904 010500	500 FT	101.500 LB	BLACK	C	#4 STR PVC BLK

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 01-24-2013

© 2016 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).