

## Workbench trolley with lowerable transport wheels, working height 840 mm

Drawers with option of partial of full extension

### Application:

The mobile workstation with versatile options for use.

### Execution:

- Welded sheet steel construction equipped with one workbench top panel made of solid beechwood, 40 mm thick
- With integrated lowering device for stationary use
- Suitable insert material for drawers, see no. 50485 060-265 and no. 50537 610-695
- Other equipment options available at extra cost: SOFT-CLOSE for drawers, see no. 50392 005, ELECTRONIC CODE combination lock, see no. 50392 010

### Advantage:

- The workbench can easily be lifted and lowered by simply turning the lever on the front side
- The workbench trolley is absolutely stable when lowered
- When you buy this product, you plant a tree and also receive a tree certificate!



|  |  |
|--|--|
| <b>Art. no.</b>  | <b>50285 245</b>                             |
| <b>Brand</b>   | HK   |
| <b>Manufacturer Part Number</b>  | 50285245                                     |
| <b>Number of fixed rollers</b>   | 2 PCS  |
| <b>Working height</b>  | 882 mm                                       |
| <b>Number of steering rollers</b>                                      | 2 PCS  |
| <b>Worktop width</b>   | 1660 mm                                      |
| <b>Number of drawers</b>   | 8 PCS  |
| <b>Worktop height</b>  | 40 mm  |
| <b>Worktop depth</b>   | 700 mm                                       |
| <b>Pullout type</b>  | Partial extension                            |
| <b>On castors</b>  | Yes  |
| <b>Moving device, can be lowered</b>                                   | Yes  |
| <b>Colour of front</b>   | Optional                                     |
| <b>Cabinet colour</b>  | Optional                                     |
| <b>With single pull-out safety brake</b>                               | Yes  |
| <b>Surface</b>   | Powder-coated                                |
| <b>With wheel lock</b>   | Yes  |
| <b>Load-carrying capacity</b>  | 720 kg                                       |
| <b>Dynamic load-carrying capacity</b>                                  | 540 kg                                       |
| <b>Wheel diameter</b>  | 160 mm                                       |
| <b>Type</b>  | mobile/retractable                           |
| <b>Lock type</b>   | DOM® locking system                          |
| <b>Material of worktop</b>   | Solid beech                                  |
| <b>Drawer front height</b>   | 2 x 60 mm, 2 x 90 mm, 2 x 150 mm, 2 x 180 mm |
| <b>Material</b>  | Sheet steel                                  |
| <b>Drawer width (inner dimension)</b>                                  | 450 mm                                       |
| <b>Drawer width (inner dimension) x drawer depth (inner dimension)</b> | 450 x 600 mm                                 |
| <b>Drawer depth (inner dimension)</b>                                  | 600 mm                                       |
| <b>Load-carrying capacity per drawer</b>                               | 100 kg                                       |
| <b>Material of wheel</b>   | Solid rubber                                 |
| <b>Central locking</b>   | Yes  |
| <b>Gross Weight</b>  | 195.000 kg                                   |
| <b>Product Group</b>   | 501  |

### EAN

4039247470693