

Torque wrench with reversible ratchet, adjustable from 1 to 320 Nm

With calibration certificate according to DIN EN ISO 6789

ATORN

Application

For controlled tightening in a clockwise direction with a high degree of accuracy



Version

- The torque is set by turning the handle
- With lever ratchet, suitable only for controlled clockwise tightening.
- Haptic and acoustic adjustment aid
- Audible and perceptible release when the set value is reached
- Dual scale with Nm and lbf.ft. display
- Ergonomically shaped handle with comfortable, textured surface
- Rapid securing and opening via the locking ring

Advantage

- Robust tubular design
- Reversible ratchet with locking push button
- Viewing window protects scale from damage

Delivery

Secure and safe transport/storage in handy cylindrical package

| | |
|---|------------------|
| Art. no. | 52240 060 |
| Tip size | 3/8 inch |
| Min./max. torque measuring range | 10-60 Nm |
| Scale value torque | 0.5 Nm |
| Length | 355 mm |
| With scale | Yes |
| Error limit (%) | 3 % |

EAN-Code

4050293367560