

## Quick-action couplings NW 7.2

One-handed quick-action coupling



### Application:

Applications: Pneumatics, mechanical and plant engineering, instrumentation and control systems, manufacturing industry, medical technology, chemical/pharmaceutical industry, workshops, automotive.

### Execution:

- Single-sided lock design
- When using steel nipples, this coupling can also be used on pneumatic tools thanks to its hardened locking pins.
- Couplings and nipples with sealing thread coating
- Ready-to-assemble polyacrylate thread coating for instant and high-level sealing without curing.

### Advantage:

- The closed locking sleeve prevents contamination of the internal parts.



<b>Art. no.</b>	<b>75101 305</b>
<b>Brand</b>	RIEGLER
<b>Manufacturer Part Number</b>	115648
<b>Connection</b>	LW 9
<b>Nominal width</b>	7.2 mm
<b>Flow rate</b>	1000 l/min
<b>Max. operating pressure</b>	35 bar
<b>Min. operating pressure</b>	0 bar
<b>Min./max. operating pressure</b>	0-35 bar
<b>Length</b>	54 mm
<b>Min./max. ambient temperature</b>	-20 to 100 °C
<b>Min./max. working temperature</b>	-20 to 100 °C
<b>Material of gasket</b>	Nitrile butadiene rubber (NBR)
<b>Material of spring</b>	Corrosion resistant steel
<b>Material of housing</b>	Brass
<b>Material of sleeve</b>	Brass
<b>Material of snap ring</b>	Stainless steel
<b>Material of pin</b>	Stainless steel
<b>Material of valve</b>	Brass
<b>Gross Weight</b>	0.057 kg
<b>Product Group</b>	7AD

### EAN

4047322059787