
4mm Banana Plug - Plug Stackable Patchcord - 2.5mm² PVC





Applications

General purpose electric and electronic testing, controlling and measuring.

Specifications

Connector Type A : Stacking 4mm Banana Plug
Connector Type B : Stacking 4mm Banana Plug

Voltage Rating : ≤33V AC/≤70V DC

Current Rating : 36A

Resistance : 250mm: 12m Ω

500mm: 15mΩ 1m: 20mΩ 2m: 30mΩ

Cable : 2.5mm², PVC

Contact Material : Brass and Beryllium Copper, Nickel Plated / Gold Nickel Plated

Insulator Material : Polyamide and Polypropylene

Temperature : -20°C to +80°C

Part Number Table

Description	Insulator Colour	Lead Length	Part Number
Test Lead, Stacking 4mm Banana Plug to Plug, 2.5mm2 PVC, 33V AC/70V DC, 36A	Blue	500mm	72-13880
	Green		72-13888
	White	1m	72-13804
	Yellow		72-13808
	Purple		72-13816
	Yellow	2m	72-13840
Test Lead, Stacking 4mm Banana Plug to Plug, Gold Contact, 2.5mm ² PVC, 33V AC/70V DC, 36A	White	250mm	72-13848
	Blue		72-13850
	Green		72-13860
	Brown	500mm	72-13866
	Grey		72-13868

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands



4mm Banana Plug - Plug Stackable Patchcord - 2.5mm² PVC



Description	Insulator Colour	Lead Length	Part Number
Test Lead, Stacking 4mm Banana Plug to Plug, Gold Contact, 2.5mm ² PVC, 33V AC/70V DC, 36A	Yellow	500mm	72-13870
	Black		72-13872
	Brown	1m	72-13788
	Yellow		72-13792
	Yellow/Green		72-13794
	Red		72-13798
	Purple		72-13802
	White	2m	72-13818
	Blue		72-13820
	Brown		72-13822
	Black		72-13830
	Green		72-13834
	Purple		72-13836

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

