

Combi thread bit set

For universal use up to 700 N/mm²

ORION[®]

Application:

For producing metric threads (drill, thread, deburr and clean thread in one operation!) for portable use on cordless drill screwdrivers and hand drills in clockwise rotation and anti-clockwise rotation in steel, non-ferrous metals and (cast iron) material groups up to a strength of 700 N/mm² up to 1xD thread depth in single-part production.

Execution:

- Precision-ground, right-hand screw tap set with drill step and 1/4" hexagon drive, HSS for M3, M4, M5, M6, M8, M10 for high requirements in terms of process reliability and service life

Advantage:

- Standard geometry with very good price/performance ratio
- High productivity, since drilling, thread de-burring and thread cleaning are achieved in one operation
- Robust metal box protects the tool from damage and contamination



Art. no.	13407 200
Brand	ORION
Manufacturer Part Number	13407200
Thread type	Metric thread
Cutting material	HSS
Hole type	Clearance hole ≤ 1xD
Composition of set	1 of each combi screw tap bit M3/M4/M5/M6/M8/M10
Gross Weight	0.253 kg
Product Group	1DB

EAN

4039247071807