



# CABLETRACKER™

Network Cable and Port Identifier

DESIGNED SPECIFICALLY FOR NETWORK

MAINTENANCE PROFESSIONALS

- Activate Link Lights to Identify a Connected Hub or Switch Port
- Transmits Four Audible Tones
- RJ-45 Male or Female Connection
- Detachable DMM Alligator Clips
- Detects Short in Tested Wire Pair
- Non-conductive probe tip
- Power "On" indicator
- Volume Control
- Ergonomically Designed



## **CABLETRACKER Network ID Kit**

The CABLETRACKER Network Tone and Probe Kit model CTK1015 is designed for network managers and technicians. Toning an active LAN circuit can disrupt network traffic and is difficult to track due to cable twist and tone bleed. The CABLETRACKER Network Tone and Probe Kit features a Port ID function that blinks the link light verifying cable connectivity. This feature also provides a simple and effective method to identify switch or hub port assignments on active networks. Three different blink rates are provided to ensure compatibility with equipment from a wide range of manufacturers. Traditional toning with two different tone frequencies and patterns is provided for non-active circuit tracing.



## Product Features

### Blink the Lights to ID Ports


Tone and probe kits were designed for one primary mission, to identify the termination point of a cable. Unfortunately, these were designed for telephony, not network maintenance. In the Networking environment cable terminations typically end in hub or switch ports. The CableTracker incorporates three link light activation speeds (blink rates) to easily identify the cable termination port by simply looking for the corresponding blink rate on the port light. Three speeds ensure the widest compatibility available.

### Easy Ethernet or Telephony Connection

Most toners on the market offer RJ-11 hard-wired modular connection. That's because they were designed mostly to be used in the Telecommunication market. This does nothing for the Lan technician who is faced with ethernet RJ-45 jacks or patch cords. The CableTracker Network ID Kit was designed to accommodate both Computer Network cabling and Telephony cabling. The Signal Generator (CT10) incorporates a female RJ-45 jack and detachable alligator clips for punch down blocks or unterminated cables.

### Time Saving Features

The CableTracker incorporates several time and money saving features not found on other Tone and Probe kits. The RJ-45 male connection and the alligator clips are detachable, meaning cord failure won't obsolete the your tester. Auto Power Down extends battery life and a built-in low battery circuit warns when battery replacement is required, saving unexpected down time searching for a new battery when the tester just goes dead. The CableTracker Probe (CT15) incorporated volume control, non-conductive plastic tip and complete compatibility with existing toners on the market.



Activate Link Lights to Identify a Connected Hub or Switch Port

## Specifications

### Physical

Signal Generator - CT10

Dimensions:  3.0 in. x 2.4 in. x 1.4 in.  
 7.6 cm x 6.6 cm x 3.6 cm

Probe - CT15

Dimensions:  8.0 in. x 1.4 in x 1.5 in  
 20.3 cm x 3.6 cm x 3.8 cm

### Signal Frequencies - CT10

Lo Tone - 1kHz; Hi Tone - 8kHz

### Reception Frequencies - CT15

Broadband 100Hz-10kHz

### Power

One 9 volt Battery Each (not supplied)

### Environment

Operating Temperature: 0° to 50°C

Storage Temperature: -10° to 55°C

Product design and specifications subject to change without notice.

## Ordering Information

### CABLETRACKER Network ID Kit

Model Number - *CTK1015*

Includes:  CT10 - Signal Generator  
 CT15 - Probe  
 CC2 - Carrying Case  
 Alligator Clip Leads  
 RJ-45 Patch Cable  
 Users Guide

### CABLETRACKER Signal Generator

Model Number - *CT10*

Includes:  CT10 - Signal Generator  
 Alligator Clip Leads  
 RJ-45 Patch Cable  
 Users Guide

### CABLETRACKER Probe

Model Number - *CT15*

Includes:  CT15 - Probe  
 Users Guide

### Accessories: (sold separately)

CC2 - Carrying Case  
 Alligator Clip Leads (6" red/black)  
 RJ-45 Patch Cable (8")

### Psiber Data Systems Inc

7075-K Mission Gorge Road  
San Diego, California 92120 USA

Phone:  619-287-9970

FAX:  619-287-9978

Internet: [www.psiber.com](http://www.psiber.com)

e-mail: [info@psiber.com](mailto:info@psiber.com)

© 2003 Psiber Data Systems Inc.  
All Rights Reserved. The Psiber Logo,  
psiber, and CABLETRACKER are trademarks of  
Psiber Data Systems Inc.

0101-1015-0001 4/03 Printed in U.S.A.

