



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
G	02	P	LTR	DESCRIPTION	DATE	DWN	APVD
		M2		REVISED PER ECO-11-004820	11MAR11	RK	HMR

AMP WIRE RANGE	AMP INSULATION RANGE
22-16 AWG 0.3-1.5 mm ²	.140 MAX DIA 3.5 MAX DIA



- △1 ASTERISK * FOR PHOS BRONZE VERSION ONLY
- △2 OBSOLETE W/O REPLACEMENT



△2 OBSOLETE	GOLD	PHOS BRONZE	165565-6	
△2 OBSOLETE	GOLD	BRASS	165565-5	
△2 OBSOLETE	SILVER	PHOS BRONZE	165565-4	
△2 OBSOLETE	SILVER	BRASS	165565-3	
	2-165565-2	TIN	PHOS BRONZE	165565-2
	2-165565-1	TIN	BRASS	165565-1
	PN ON TAPE	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN jr_ruth 15APR05	STE TE Connectivity	
DIMENSIONS: mm		CHK T MICHELUTTI 15APR05		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T MICHELUTTI 15APR05	NAME RECEPTACLE, FASTON, PIDG, .110 SERIES	
0 PLC ± -		PRODUCT SPEC	-	
1 PLC ± 0.2		APPLICATION SPEC	-	
2 PLC ± -		WEIGHT	-	
3 PLC ± -		SIZE	CAGE CODE	DRAWING NO
4 PLC ± -		A3 00779		C-165565
ANGLES ± 5°		CUSTOMER DRAWING		RESTRICTED TO
MATERIAL		SCALE 5:1		SHEET 1 OF 1
FINISH		REV M2		