

Miniature cutting insert, type AF HC56 15

for axial recessing

ATORN[®]

Application

For axial recessing in the material groups of steel and (stainless steel) with low to high cutting speeds and medium cutting conditions.



Version

- solid carbide cutting insert with inner cooling

Advantage

- very hard cemented carbide type ensures low wear
- sturdy geometry for axial cutter insert
- innovative coating technology for universal use with extremely demanding service life requirements

Art. no.	17131 200
Shaft diameter	8 mm
ISO name	AF
Length	64 mm
Clearance length	22 mm
Recessing width	2.5 mm
Plunge depth	3.5 mm
Programming size	3.95 mm
Min. bore diameter	10 mm
Machining direction	Right
Carbide type	HC56 15
Material to be processed	Steel, Stainless steel, Special alloy, Hardened material

EAN-Code

4050293379112