

SCLC clamp holder with internal cooling, positive

For facing and longitudinal turning using CC indexable inserts

ATORN[®]

Application

For face and longitudinal turning with CC indexable insert 80°

Version

- precision-made steel carrier with high-performance cooling system, nickel-plated, hardened, type C, attack angle 95°, tip angle 80°, clearance angle 7°

Advantage

- high-performance cooling channel system with three outlets ensures an extremely long service life and reliable working
- universal use for facing and longitudinal turning
- positive body geometry ensures low cutting forces
- Very good surface quality for medium infeed and finishing



Art. no.	17830 710
ISO name	SCLC R/L 2020 K09 IK G1/8
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Length of head	17 mm
Programming size	25 mm
Suitable for indexable inserts	CC.. 09T3..
Tool design	Right
DIN	4983

EAN-Code

4050293566284