

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** PLASTI-KOTE® STAIN BLOCK WHITE 400 ML
- **Article number:** 440.0071019.076
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Sector of Use**
 - SU21 Consumer uses: Private households / general public / consumers
 - SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- **Product category** PC9a Coatings and paints, thinners, paint removers
- **Process category**
 - PROC7 Industrial spraying
 - PROC11 Non industrial spraying
- **Application of the substance / the mixture** Paint
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
MOTIP DUPLI B.V.
Wolfraamweg 2
NL-8471 XC Wolvega
Nederland
Tel : +31 (0)561 694400
Fax: +31 (0)561 694411
e-mail: info@nl.motipdupli.com
- **Further information obtainable from:** Department Product Safety
- **1.4 Emergency telephone number:** +31 (0)561-694400 (09:00h - 17:00h)

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.



GHS07

Eye Irrit. 2 H319 Causes serious eye irritation.
STOT SE 3 H336 May cause drowsiness or dizziness.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms**



GHS02



GHS07

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 62

Revision: 12.01.2018

Trade name: PLASTI-KOTE® STAIN BLOCK WHITE 400 ML

(Contd. of page 1)

· **Signal word** *Danger*· **Hazard-determining components of labelling:***acetone**Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics**butanone*· **Hazard statements***H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.**H319 Causes serious eye irritation.**H336 May cause drowsiness or dizziness.*· **Precautionary statements***P101 If medical advice is needed, have product container or label at hand.**P102 Keep out of reach of children.**P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.**P211 Do not spray on an open flame or other ignition source.**P251 Do not pierce or burn, even after use.**P260 Do not breathe spray.**P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.**P501 Dispose of contents / container in accordance with regional regulations.*· **Additional information:***EUH066 Repeated exposure may cause skin dryness or cracking.*· **2.3 Other hazards**· **Results of PBT and vPvB assessment**· **PBT:** Not applicable.· **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

· **3.2 Chemical characterisation: Mixtures**· **Description:** Mixture of substances listed below with nonhazardous additions.· **Dangerous components:**

CAS: 67-64-1 EINECS: 200-662-2 Index number: 606-001-00-8 Reg.nr.: 01-2119471330-49	<i>acetone</i> ⚠ Flam. Liq. 2, H225 ⚠ Eye Irrit. 2, H319; STOT SE 3, H336	12.5-<20%
CAS: 74-98-6 EINECS: 200-827-9 Index number: 601-003-00-5 Reg.nr.: 01-2119486944-21	<i>propane</i> ⚠ Flam. Gas 1, H220 Press. Gas C, H280	10-<12.5%
CAS: 106-97-8 EINECS: 203-448-7 Index number: 601-004-00-0 Reg.nr.: 01-2119474691-32	<i>butane (containing ≥0,1 % butadiene (203-450-8))</i> ⚠ Flam. Gas 1, H220 Press. Gas C, H280	5-<10%
CAS: 75-28-5 EINECS: 200-857-2 Index number: 601-004-00-0 Reg.nr.: 01-2119485395-27	<i>isobutane</i> ⚠ Flam. Gas 1, H220 Press. Gas C, H280	5-<10%

(Contd. on page 3)

GB

Safety data sheet
according to 1907/2006/EC, Article 31









Printing date 22.06.2018

Version number 62

Revision: 12.01.2018

Trade name: PLASTI-KOTE® STAIN BLOCK WHITE 400 ML

(Contd. of page 2)

EC number: 919-857-5 Reg.nr.: 01-2119463258-33	Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics  Flam. Liq. 3, H226  Asp. Tox. 1, H304  STOT SE 3, H336	5-<10%
CAS: 1330-20-7 EINECS: 215-535-7 Index number: 601-022-00-9 Reg.nr.: 01-2119488216-32-xxxx	xylene  Flam. Liq. 3, H226  STOT RE 2, H373; Asp. Tox. 1, H304  Acute Tox. 4, H312; Acute Tox. 4, H332; Skin Irrit. 2, H315; Eye Irrit. 2, H319; STOT SE 3, H335 Aquatic Chronic 3, H412	2.5-<5%
CAS: 78-93-3 EINECS: 201-159-0 Index number: 606-002-00-3 Reg.nr.: 01-2119457290-43	butanone  Flam. Liq. 2, H225  Eye Irrit. 2, H319; STOT SE 3, H336	<2.5%

Additional information:

Note C (Regulation (EC) no. 1272/2008) applies to the component Xylene (mixture) CAS: 1330-20-7.
For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:**
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.
- **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **5.2 Special hazards arising from the substance or mixture**
During heating or in case of fire poisonous gases are produced.
- **5.3 Advice for firefighters -**
- **Protective equipment:** Mouth respiratory protective device.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Mount respiratory protective device.
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.

(Contd. on page 4)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 62

Revision: 12.01.2018

Trade name: **PLASTI-KOTE® STAIN BLOCK WHITE 400 ML**

(Contd. of page 3)

See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.
- **Information about fire - and explosion protection:**
Do not spray onto a naked flame or any incandescent material.
Keep ignition sources away - Do not smoke.
Keep respiratory protective device available.
Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**
Observe official regulations on storing packagings with pressurised containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep container tightly sealed.
- **Storage class:** 2 B
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:****67-64-1 acetone**

WEL	Short-term value: 3620 mg/m ³ , 1500 ppm
	Long-term value: 1210 mg/m ³ , 500 ppm

106-97-8 butane (containing ≥ 0,1 % butadiene (203-450-8))

WEL	Short-term value: 1810 mg/m ³ , 750 ppm
	Long-term value: 1450 mg/m ³ , 600 ppm
	Carc (if more than 0.1% of buta-1.3-diene)

1330-20-7 xylene

WEL	Short-term value: 441 mg/m ³ , 100 ppm
	Long-term value: 220 mg/m ³ , 50 ppm
	Sk; BMGV

78-93-3 butanone

WEL	Short-term value: 899 mg/m ³ , 300 ppm
	Long-term value: 600 mg/m ³ , 200 ppm
	Sk, BMGV

· **Ingredients with biological limit values:****1330-20-7 xylene**

BMGV	650 mmol/mol creatinine
	Medium: urine
	Sampling time: post shift
	Parameter: methyl hippuric acid

78-93-3 butanone

BMGV	70 µmol/L
	Medium: urine
	Sampling time: post shift
	Parameter: butan-2-one

- **Additional information:** The lists valid during the making were used as basis.

(Contd. on page 5)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 62

Revision: 12.01.2018

Trade name: PLASTI-KOTE® STAIN BLOCK WHITE 400 ML

(Contd. of page 4)

· 8.2 Exposure controls**· Personal protective equipment:****· General protective and hygienic measures:***Keep away from foodstuffs, beverages and feed.**Immediately remove all soiled and contaminated clothing**Wash hands before breaks and at the end of work.**Do not inhale gases / fumes / aerosols.**Avoid contact with the eyes and skin.**Avoid contact with the eyes.***· Respiratory protection:***In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.***· Protection of hands:***The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.**Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.**Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation***· Material of gloves***The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.***· Penetration time of glove material***Butyl rubber gloves with a thickness of 0.4 mm are resistant to:**Acetone: 480 min**Butyl acetate: 60 min**Ethyl acetate: 170 min**Xylene: 42 min**The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.***· Eye protection:***Tightly sealed goggles***SECTION 9: Physical and chemical properties****· 9.1 Information on basic physical and chemical properties****· General Information****· Appearance:****Form:** Aerosol**Colour:** White**· Odour:** Solvent-like**· Odour threshold:** Not determined.**· pH-value:** Not determined.**· Change in condition****Melting point/freezing point:** Undetermined.**Initial boiling point and boiling range:** Not applicable, as aerosol.**· Flash point:** <0 °C (<32 °F)
Not applicable, as aerosol.**· Flammability (solid, gas):** Not applicable.

(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 62

Revision: 12.01.2018

Trade name: **PLASTI-KOTE® STAIN BLOCK WHITE 400 ML**

(Contd. of page 5)

· Ignition temperature:	365 °C (689 °F)
· Decomposition temperature:	Not determined.
· Auto-ignition temperature:	Product is not selfigniting.
· Explosive properties:	Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
· Explosion limits:	
Lower:	1.7 Vol %
Upper:	13 Vol %
· Vapour pressure at 20 °C (68 °F):	3,500 hPa (2,625.2 mm Hg)
· Density at 20 °C (68 °F):	1.11 g/cm ³ (9.26 lbs/gal)
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not applicable.
· Solubility in / Miscibility with water:	Not miscible or difficult to mix.
· Partition coefficient: n-octanol/water:	Not determined.
· Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
· Solvent content:	
Organic solvents:	59.3 %
· EU-VOC:	657.7 g/l
· EU-VOC in %:	59.45 %
· VOC (EC)	---
	656.3 g/l
· VOC-EU%	59.33 %
· Solids content:	46.4 %
· 9.2 Other information	No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.

· LD/LC50 values relevant for classification:

67-64-1 acetone

Oral	LD50	5,800 mg/kg (rat)
Dermal	LD50	>15,800 mg/kg (rabbit)
Inhalative	LC50 / 4h	76 mg/l (rat)

(Contd. on page 7)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 62

Revision: 12.01.2018

Trade name: PLASTI-KOTE® STAIN BLOCK WHITE 400 ML

(Contd. of page 6)

1330-20-7 xylene

Oral	LD50	3,523 mg/kg (rat)
Dermal	LD50	2,000 mg/kg (rabbit)
Inhalative	LC50 / 4 h	29,000 mg/m ³ (rat)

78-93-3 butanone

Oral	LD50	>2,193 mg/kg (rat)
Dermal	LD50	>5,000 mg/kg (rabbit)
Inhalative	LC50 / 4 h	34 mg/m ³ (rat)

- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation**
Causes serious eye irritation.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure**
May cause drowsiness or dizziness.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information· **12.1 Toxicity**· **Aquatic toxicity:****67-64-1 acetone**

LC50/96h	8,300 mg/l (fish)
EC50/96h	7,200 mg/l (algae)
LC50 / 48 h	8,450 mg/l (crustacean (water flea))

1330-20-7 xylene

EC50 / 48 h	7.4 mg/l (daphnia magna)
LC50 / 96 h	13.5 mg/l (fish)

78-93-3 butanone

LC50 / 48 h	308 mg/l (daphnia magna)
LC50 / 72 h	1,972 mg/l (Pseudokirchneriella Subcapitata)
LC50 / 96 h	2,990 mg/l (fish)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.

· **Additional ecological information:**· **General notes:**

Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water
Do not allow product to reach ground water, water course or sewage system.
Danger to drinking water if even small quantities leak into the ground.

· **12.5 Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

GB

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 62

Revision: 12.01.2018

Trade name: **PLASTI-KOTE® STAIN BLOCK WHITE 400 ML**

(Contd. of page 7)

SECTION 13: Disposal considerations

· **13.1 Waste treatment methods**

· **Recommendation**

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

· **European waste catalogue**

08 01 11*	waste paint and varnish containing organic solvents or other hazardous substances
15 01 04	metallic packaging

· **Uncleaned packaging:**

· **Recommendation:** Non contaminated packagings may be recycled.

SECTION 14: Transport information

· **14.1 UN-Number**

· **ADR, IMDG, IATA** UN1950

· **14.2 UN proper shipping name**

· **ADR** 1950 AEROSOLS
 · **IMDG** AEROSOLS
 · **IATA** AEROSOLS, flammable

· **14.3 Transport hazard class(es)**

· **ADR**



· **Class** 2 5F Gases.
 · **Label** 2.1

· **IMDG, IATA**



· **Class** 2.1
 · **Label** 2.1

· **14.4 Packing group**

· **ADR, IMDG, IATA** not regulated

· **14.5 Environmental hazards:** Not applicable.

· **14.6 Special precautions for user**

· **Danger code (Kemler):** -
 · **EMS Number:** F-D,S-U
 · **Stowage Code** SW1 Protected from sources of heat.
 SW22 For AEROSOLS with a maximum capacity of 1 litre:
 Category A. For AEROSOLS with a capacity above 1 litre:
 Category B. For WASTE AEROSOLS: Category C, Clear
 of living quarters.

(Contd. on page 9)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 62

Revision: 12.01.2018

Trade name: PLASTI-KOTE® STAIN BLOCK WHITE 400 ML

(Contd. of page 8)

· Segregation Code	SG69 For AEROSOLS with a maximum capacity of 1 litre: Segregation as for class 9. Stow "separated from" class 1 except for division 1.4. For AEROSOLS with a capacity above 1 litre: Segregation as for the appropriate subdivision of class 2. For WASTE AEROSOLS: Segregation as for the appropriate subdivision of class 2.
· 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code	Not applicable.
· Transport/Additional information:	
· ADR	
· Limited quantities (LQ)	1L
· Excepted quantities (EQ)	Code: E0 Not permitted as Excepted Quantity Code: E0 Not permitted as Excepted Quantity
· Transport category	2
· Tunnel restriction code	D
· IMDG	
· Limited quantities (LQ)	1L
· Excepted quantities (EQ)	Code: E0 Not permitted as Excepted Quantity Code: E0 Not permitted as Excepted Quantity
· UN "Model Regulation":	UN 1950 AEROSOLS, 2.1

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **Seveso category P3a** FLAMMABLE AEROSOLS
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 150 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3, 40
- **National regulations:**
- **Other regulations, limitations and prohibitive regulations**
- **Substances of very high concern (SVHC) according to REACH, Article 57**
- None of the ingredients is listed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
- H220 Extremely flammable gas.
- H225 Highly flammable liquid and vapour.
- H226 Flammable liquid and vapour.
- H280 Contains gas under pressure; may explode if heated.
- H304 May be fatal if swallowed and enters airways.
- H312 Harmful in contact with skin.

(Contd. on page 10)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 22.06.2018

Version number 62

Revision: 12.01.2018

Trade name: PLASTI-KOTE® STAIN BLOCK WHITE 400 ML

(Contd. of page 9)

*H315 Causes skin irritation.**H319 Causes serious eye irritation.**H332 Harmful if inhaled.**H335 May cause respiratory irritation.**H336 May cause drowsiness or dizziness.**H373 May cause damage to the gastro-intestinal tract through prolonged or repeated exposure.**H412 Harmful to aquatic life with long lasting effects.***· Abbreviations and acronyms:***RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)**ICAO: International Civil Aviation Organisation**ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)**IMDG: International Maritime Code for Dangerous Goods**IATA: International Air Transport Association**GHS: Globally Harmonised System of Classification and Labelling of Chemicals**EINECS: European Inventory of Existing Commercial Chemical Substances**ELINCS: European List of Notified Chemical Substances**CAS: Chemical Abstracts Service (division of the American Chemical Society)**VOC: Volatile Organic Compounds (USA, EU)**LC50: Lethal concentration, 50 percent**LD50: Lethal dose, 50 percent**PBT: Persistent, Bioaccumulative and Toxic**SVHC: Substances of Very High Concern**vPvB: very Persistent and very Bioaccumulative**Flam. Gas 1: Flammable gases – Category 1**Aerosol 1: Aerosols – Category 1**Press. Gas C: Gases under pressure – Compressed gas**Flam. Liq. 2: Flammable liquids – Category 2**Flam. Liq. 3: Flammable liquids – Category 3**Acute Tox. 4: Acute toxicity – Category 4**Skin Irrit. 2: Skin corrosion/irritation – Category 2**Eye Irrit. 2: Serious eye damage/eye irritation – Category 2**STOT SE 3: Specific target organ toxicity (single exposure) – Category 3**STOT RE 2: Specific target organ toxicity (repeated exposure) – Category 2**Asp. Tox. 1: Aspiration hazard – Category 1**Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard – Category 3***· * Data compared to the previous version altered.**

GB