

Pneumatic straight grinder SARH 820

300 watt



Application:

For milling, roughing and rough machining.

Execution:

- With double bearing of the drive spindle for particularly quiet running during milling work
- Controlled speed, for constant speeds and low air consumption when idling
- With energy-saving motor technology

Delivery:

With 6-mm collet chuck and key for changing tools, in box



Art. no.	75036 280
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150021125
Model	SARH 820
Valve design	Lever valve
Max. idle speed	20000 rpm
Power output	300 W
Air consumption	500 l/min
Connection thread	R 1/8 inch
Inner hose diameter	7 mm
Length	221 mm
Diameter of housing	38 mm
Max. clamping diameter	8 mm
Suitable for max. sanding block diameter	24 mm
Max. HM rotating milling cutter diameter	12 mm
Weight	0.83 kg
Gross Weight	1.440 kg
Product Group	748