

MAGNETIC SWITCH SWITCH BLOCK,  
RECTANGULAR LARGE 25X88 MM, CONTACTS  
1NC/1NO, WITH M8 PLUG 4-POLE, PIN ASSIGN.:  
PIN1=21, PIN2=22, PIN3=13, PIN4=14



Figure similar

Product designation		magnetically operated switch, switch block
Design of the product		rectangular sensor unit
<b>General technical data:</b>		
<b>Product function</b>		
<ul style="list-style-type: none"> <li>positive opening</li> </ul>		No
<b>Shock resistance</b>		
<ul style="list-style-type: none"> <li>acc. to IEC 60068-2-27</li> </ul>		Sinusoidal half-wave 30g / 11 ms
<b>Vibration resistance</b>		
<ul style="list-style-type: none"> <li>acc. to IEC 60068-2-6</li> </ul>		10 ... 55 Hz: 1 mm
<b>Protection class IP</b>		IP67
<b>Equipment marking</b>		
<ul style="list-style-type: none"> <li>acc. to DIN EN 61346-2</li> <li>acc. to DIN EN 81346-2</li> </ul>		S S
<b>Enclosure:</b>		
<b>Design of the housing</b>		block
<b>Material of the enclosure</b>		plastic
<b>Drive Head:</b>		
<b>Design of the operating mechanism</b>		magnet
<b>Design of the switching function</b>		NC contact and NO contact
<b>Connections/ Terminals:</b>		
<b>Type of electrical connection</b>		connector M8
<b>Safety related data:</b>		
<b>Safety Integrity Level (SIL) acc. to IEC 61508</b>		SIL3

Performance level (PL) acc. to EN ISO 13849-1		e
Category acc. to EN 954-1		4

#### Ambient conditions:

<b>Ambient temperature</b>		
• during operation	°C	-25 ... +70
• during storage and transport	°C	-25 ... +70

#### Inputs/ Outputs:

<b>Type of switching output</b>		Reed contacts
---------------------------------	--	---------------

#### Display:

<b>Evaluation version required</b>		yes
------------------------------------	--	-----

#### Installation/ mounting/ dimensions:

<b>Mounting type</b>		screw fixing
----------------------	--	--------------

#### Certificates/ approvals:

General Product Approval	Functional Safety/Safety of Machinery	Declaration of Conformity	other
--------------------------	---------------------------------------	---------------------------	-------



[Type Examination Certificate](#)

[other](#)



EG-Konf.

[other](#)

#### Further information

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

##### Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

##### Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3SE66052BA01>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SE66052BA01/all>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=3SE66052BA01&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=3SE66052BA01&lang=en)



last modified:

09.03.2015