

SIPLUS ET200M SEPARATOR BUS MOD F; -25 ... +60 DEGREES C WITH CONFORMAL COATING BASED ON 6ES7195-7HG00-0XA0



Figure similar

Standards, approvals, certificates

CE mark	Yes
KC approval	Yes
UL approval	Yes; File E239877
RCM (formerly C-TICK)	Yes
FM approval	No
EAC (formerly Gost-R)	Yes

Ambient conditions

Ambient temperature in operation	
• Min.	-25 °C; = Tmin
• max.	60 °C; = Tmax
Extended ambient conditions	
• Relative to ambient temperature-atmospheric pressure-installation altitude	Tmin ... Tmax at 1080 hPa ... 795 hPa (-1000 m ... +2000 m)
Relative humidity	
— With condensation, tested in accordance with IEC 60068-2-38, max.	100 %; RH incl. condensation/frost (no commissioning under condensation conditions)
Resistance	
— against biologically active substances / conformity with EN 60721-3-3	Yes
— against chemically active substances / conformity with EN 60721-3-3	Yes
— against mechanically active substances / conformity with EN 60721-3-3	Yes

Accessories

belongs to product

ET 200M

Weights

Weight, approx.

10 g

last modified:

12.03.2015