


# MFS201



## Magnetic sensor

MFB3060-BPKG/M/ZH



### Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	60; (referred to magnet M 4.0)
Housing	threaded type
Dimensions [mm]	M12 x 1 / L = 50

### Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Protection class	II
Reverse polarity protection	yes

### Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	5000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

### Detection zone

Sensing range [mm]	60; (referred to magnet M 4.0)
Response sensitivity [mT]	1.2

### Accuracy / deviations

Hysteresis [% of Sr]	1...10
----------------------	--------

### Operating conditions

Ambient temperature [°C]	-25...75
Protection	IP 67


# MFS201



## Magnetic sensor

MFB3060-BPKG/M/ZH

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5 kV line to line, Ri: 2 Ohm
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
MTTF	[years]	2680
Mechanical data		
Weight	[g]	106.5
Housing		threaded type
Dimensions	[mm]	M12 x 1 / L = 50
Thread designation		M12 x 1
Materials		housing: stainless steel; sensing face: PBT orange
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Accessories (supplied)		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PUR; 3 x 0.34 mm <sup>2</sup>		
Connection		



Core colours :

- BK = black
- BN = brown
- BU = blue