

Part Number: 72002NH

INDUSTRIAL ETHERNET EUROPE



Product Description

DataTuff Industrial ETHERNET Cat 5e 2 Pair, 26 AWG, Overall Foil + 80% Braid, No Halogen Jacket, UL AWG 21286

Technical Specifications

Product Overview			
Environmental Space:	Indoor - Euroclass Eca		
Plansie al Oherrenteriation (Orangell)			

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Construction n x D	No. o	f Pairs
26	Stranded BC - Bare Copper 7x0.16 mm 2				
Conductor Count: Total Number of Pairs:			8		
			4		
Conductor Size:		26 AW			

Insulation

Material	Nominal Diameter	Diameter +/- Tolerance
PP - Polypropylene	0.98 mm	0.05 mm

Color Chart

Number	Color
Pair 1	White/Blue & Blue
Pair 2	White/Orange & Orange

Outer Shield Material

Туре	Material	Min. Coverage [%]	
Таре	Aluminum/Polyester		
Braid	TC - Tinned Copper	80 %	
Note:	Note:		

Outer Jacket Material

Material	Color	Nominal Diameter	Diameter +/- Tolerance	Min. Wall Thickness	Nominal Wall Thickness
LSZH / FRNC (UV stabilised and oil resistant)	Black	6 mm	0.3 mm	0.8 mm	0.8 mm

Construction and Dimensions

Min Elongatio	on at Breakof Conductors:	10 %
Min Elongatio	on at Breakof Insulation:	100 %

Cabling

Description	Filler
2 pairs and 2 fillers twisted to cable core covered with a polyester for	il Polypropylene (2x)
Min Elongation at Breakof Jacket:	100 %
Min Tensile Strength of Jacket:	9 MPa

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalanced Within Pair [%]
140 Ohm/km	2 Ohm

Capacitance

Max. Capacitance Unbalance	Max. Mutual Capacitance
1.6 pF/m	56 pF/m
Shielding:	

SF/UTP - Overall Braid + Foil

Impedance

Nominal Characteristic Impedance	Nominal Characteristic Tolerance	Nominal Input Impedance
100 Ohm	5 Ohm	100 +/- 15 Ohm

Delay

Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
40 ns/100m	60 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. ACRF (ELFEXT) [dB]	Min. RL (Return Loss) [dB]
0.772 MHz		67 dB		19.4 dB
1 MHz	3.2 dB/100m	65.3 dB	63.8 dB	20 dB
4 MHz	6 dB/100m	56.3 dB	51.8 dB	23 dB
10 MHz	9.5 dB/100m	50.3 dB	43.8 dB	25 dB
16 MHz	12.1 dB/100m	47.2 dB	39.7 dB	25 dB
20 MHz	13.6 dB/100m	45.8 dB	37.8 dB	25 dB
25 MHz	15.3 dB/100m	44.3 dB	35.8 dB	24.3 dB
31.25 MHz	17.1 dB/100m	42.9 dB	33.9 dB	23.6 dB
62.5 MHz	24.8 dB/100m	38.3 dB	27.9 dB	21.5 dB
100 MHz	32 dB/100m	35.3 dB	23.8 dB	20.1 dB

Current

Element	Max. Recommended Current [A]
Conductor	1.1 A

Voltage

Voltage Rating [V] 450 V DC and 300 V AC

Temperature Range

Installation Temp Range:	-5°C To +50°C
Operating Temp Range:	-40°C To +80°C

Mechanical Characteristics

Oil Resistance:	IEC 60811-2-1
Max Recommended Pulling Tension:	40 N
Min Bend Radius (W/o Pulling Strength):	60 mm
Min Setting Radius:	30 mm

Standards

ISO/IEC Compliance:	ISO/IEC 11801 Ed. 2.2:2002/A2:2010/C1:2011 and ISO/IEC 24702
CPR Euroclass:	Eca
CENELEC Compliance:	EN 50173-1 Ed. 3:2011
Data Category:	Category 5e
ANSI Compliance:	ANSI/TIA/EIA 568-B.2-1 (2002)

Applicable Environmental and Other Programs	
EU RoHS Compliance Date (yyyy-mm-dd):	2016-01-06
Flammability, LS0H, Toxicity Testing	
ISO/IEC Flammability:	IEC 60332-1-2
Amount of Halogen acc. to IEC 60754-1 & EN50267-1:	Zero

Part Number

Variants	
Item #	Color
72002NH.02305	Black
72002NH.02500	Black
72002NH.02B100	Black
Patent:	
History	
Revision Number:	

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.