

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0008650816](#)  
**Status:** **Active**  
**Overview:** [KK® Interconnect System - Molex](#)  
**Description:** [KK 254 Crimp Terminal 6459, 22-30 AWG, Bag, Phosphor Bronze Selective Gold \(Au\)](#)

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification PK-2759-001 \(PDF\)](#)  
[Product Specification PS-10-07-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification TS-10-07-001 \(PDF\)](#)

**General**

Product Family [Crimp Terminals](#)  
Series [6459](#)  
Application [Signal, Wire-to-Board](#)  
Crimp Quality Equipment [Yes](#)  
Overview [KK® Interconnect System - Molex](#)  
Packaging Alternative [08-65-0815 \(Reel\)](#)  
Product Name [KK 254](#)  
UPC [800754227445](#)

**Physical**

Gender [Female](#)  
Material - Metal [Phosphor Bronze](#)  
Material - Plating Mating [Gold](#)  
Net Weight [0.069/g](#)  
Packaging Type [Bag](#)  
Plating min - Mating [0.381µm](#)  
Termination Interface: Style [Crimp or Compression](#)  
Wire Insulation Diameter [1.57mm max.](#)  
Wire Size AWG [22, 24, 26, 28, 30](#)  
Wire Size mm<sup>2</sup> [N/A](#)

**Solder Process Data**


Lead-freeProcess Capability [N/A](#)

**Material Info**

Engineering Number [6459-\(555\)L](#)

**Reference - Drawing Numbers**

Packaging Specification [PK-2759-001](#)  
Product Specification [PS-10-07-001, TS-10-07-001](#)  
Sales Drawing [SD-6459-001](#)



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2018 (15  
January 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[6459 Series](#)

**Use With**

[2.54mm Pitch KK Crimp Terminal Housing 2695](#)