

SWUC offset solid carbide boring bar, positive, left

For face turning and longitudinal turning using WC indexable insert

ATORN[®]



Application

For face and longitudinal turning with WC indexable insert, 80°.

Execution

- Precision-manufactured boring bar, **steel**, with internal cooling, offset, type C, attack angle 93°, tip angle 80°, clearance angle 7°

Advantage

- Universal use for face and longitudinal turning
- Positive geometry for the body ensures low cutting forces

Art. No.	17827 225
ISO name	A 0508H SWUC R/L 02
Min. bore diameter	5.8 mm
Tapered diameter	5 mm
Shaft diameter	8 mm
Clearance length	18 mm
Length	100 mm
Clamping surface height	7 mm
Programming size	2.9 mm
Suitable for indexable inserts	WC.. 0201..
Tool design	Right
DIN	8024

EAN-Code

4050293390346