

## Hinged-door cabinet housing with solid sheet metal doors, height 1950 mm

Cabinet housing without internal configuration

### Application:


For secure and clearly-visible storage of tools, accessories, files or many other parts.

### Execution:

- Robust sheet steel structure
- Integrated mounting profile enables height adjustment of accessories in the grid of 30 mm
- Forklift-compatible base with removable base fascia for transporting internally
- Can be locked using grip handle and cylinder security lock incl. 2 keys
- cabinet can be fitted with an ELECTRONIC CODE combination lock at extra charge as an option, see no. 50392 020
- Accessories for equipping with support profiles: 3 support profiles no. 50658 110-158 can be inserted per storage level. One pair of guide rails no. 50658 100 is required per storage level. Please consider when ordering.
- Accessories such as pairs of support rails, support profiles, drawers on the following pages

### Advantage:

- Using the mounting profile in the cabinet, can be optionally expanded and customised with accessories such as support profiles, drawers, shelves and perforated sheet panels



<b>Art. no.</b>	<b>50658 006</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50658006
<b>Door design</b>	Full-sheet panel
<b>Height</b>	1950 mm
<b>Width</b>	1018 mm
<b>Depth</b>	620 mm
<b>Effective height</b>	1770 mm
<b>Load-carrying capacity</b>	1000 kg
<b>With doors</b>	Yes
<b>Central locking</b>	Yes
<b>Lock type</b>	DOM® locking system
<b>Material</b>	Sheet steel
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Colour of front</b>	Anthracite grey RAL 7016
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	91.000 kg
<b>Product Group</b>	507

### EAN

4053625406333