

**SECTION 1: Identification of the substance/mixture and of the company/undertaking****1.1. Product identifier**

Product form : Mixture  
Product name : BREAKER  
Product code : 506  
Type of product : Acids,Detergent  
Product group : Mixture

**1.2. Relevant identified uses of the substance or mixture and uses advised against****1.2.1. Relevant identified uses**

Industrial/Professional use spec : Industrial  
For professional use only  
Use of the substance/mixture : Cleaner

**1.2.2. Uses advised against**

No additional information available

**1.3. Details of the supplier of the safety data sheet**

Clover Chemicals Ltd  
Clover House  
Macclesfield Road  
SK23 7DQ Whaley Bridge - United Kingdom  
T 01663 733114 - F 01663 733115  
[info@cloverchemicals.com](mailto:info@cloverchemicals.com) - [www.cloverchemicals.com](http://www.cloverchemicals.com)

**1.4. Emergency telephone number**

Country	Official advisory body	Address	Emergency number	Comment
Ireland	National Poisons Information Centre Beaumont Hospital	PO Box 1297 Beaumont Road 9 Dublin	+353 1 809 2566 (Healthcare professionals- 24/7) +353 1 809 2166 (public, 8am - 10pm, 7/7)	
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	

**SECTION 2: Hazards identification****2.1. Classification of the substance or mixture****Classification according to Regulation (EC) No. 1272/2008 [CLP]**

Skin Corr. 1 H314

Full text of hazard classes and H-statements : see section 16

**Adverse physicochemical, human health and environmental effects**

No additional information available

**2.2. Label elements****Labelling according to Regulation (EC) No. 1272/2008 [CLP]**

Hazard pictograms (CLP) :



GHS05

CLP Signal word

: Danger

Hazard statements (CLP)

: H314 - Causes severe skin burns and eye damage.

# BREAKER

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Precautionary statements (CLP) : P102 - Keep out of reach of children.  
P264 - Wash hands thoroughly after handling.  
P280 - Wear protective gloves, eye protection.  
P301+P330+P331 - IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.  
P313 - Get medical advice/attention.  
P303+P361+P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower.  
P332+P313 - If skin irritation occurs: Get medical advice/attention.  
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P337+P313 - If eye irritation persists: Get medical advice/attention.  
P362 - Take off contaminated clothing.

### 2.3. Other hazards

This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII

This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable

### 3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Phosphoric Acid	(CAS-no) 7664-38-2 (Einecs nr) 231-633-2 (EG annex nr) 015-011-00-6	10 – 30	Met. Corr. 1, H290 Acute Tox. 4 (Oral), H302 Skin Corr. 1B, H314
Isotridecanol, ethoxylated	(CAS-no) 69011-36-5 (REACH-no) polymer	1 – 3	Acute Tox. 4 (Oral), H302 Eye Dam. 1, H318
(2-Methoxymethylethoxy)propanol substance with a Community workplace exposure limit	(CAS-no) 34590-94-8 (Einecs nr) 252-104-2	1 – 3	Not classified

### Specific concentration limits:

Name	Product identifier	Specific concentration limits
Phosphoric Acid	(CAS-no) 7664-38-2 (Einecs nr) 231-633-2 (EG annex nr) 015-011-00-6	( 10 ≤C < 25) Eye Irrit. 2, H319 ( 10 ≤C < 25) Skin Irrit. 2, H315 ( 25 ≤C < 100) Skin Corr. 1B, H314

Full text of H-statements: see section 16

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

General advice

: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).

Inhalation

: Allow affected person to breathe fresh air. Allow the victim to rest.

Skin contact

: Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse.

Eye contact

: Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persists.

Ingestion

: Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

### 4.2. Most important symptoms and effects, both acute and delayed

Acute effects skin

: Causes skin irritation. Red skin.

Acute effects eyes

: Causes serious eye damage. redness, itching, tears.

Acute effects oral route

: Burns or irritation of the linings of the mouth, throat, and gastrointestinal tract. Abdominal pain, nausea.

### 4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

Suitable extinguishing media

: Water.

### 5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire

: Toxic fumes may be released. Carbon dioxide. Carbon monoxide.

# BREAKER

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.  
Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

#### 6.1.1. For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

#### 6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.  
Emergency procedures : Ventilate area.

### 6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.

### 6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour.

### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep container tightly closed.  
Incompatible products : Strong bases.  
Packaging materials : polyethylene.

### 7.3. Specific end use(s)

No additional information available

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

<b>(2-Methoxymethylethoxy)propanol (34590-94-8)</b>	
<b>EU - Occupational Exposure Limits</b>	
IOELV TWA (mg/m <sup>3</sup> )	308
IOELV TWA (ppm)	50 ppm

<b>Phosphoric Acid (7664-38-2)</b>	
<b>EU - Occupational Exposure Limits</b>	
Local name	Orthophosphoric acid
IOELV TWA (mg/m <sup>3</sup> )	1 mg/m <sup>3</sup>
IOELV STEL (mg/m <sup>3</sup> )	2 mg/m <sup>3</sup>
<b>United Kingdom - Occupational Exposure Limits</b>	
Local name	Orthophosphoric acid
WEL TWA (mg/m <sup>3</sup> )	1 mg/m <sup>3</sup>
WEL STEL (mg/m <sup>3</sup> )	2 mg/m <sup>3</sup>

### 8.2. Exposure controls

#### Personal protective equipment:

Avoid all unnecessary exposure.

#### Hand protection:

Wear protective gloves.

# BREAKER

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### Eye protection:

Chemical goggles or safety glasses

### Protective equipment:

Wear suitable protective clothing. Acid resistant clothing

### Personal protective equipment symbol(s):



### Other information:

Do not eat, drink or smoke during use.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Physical state/form	: Liquid.
Colour	: Colourless.
Odour	: odourless.
Odour threshold	: No data available
pH	: ≤ 1.5
Relative evaporation rate (butylacetate=1)	: No data available
Melting point/range	: < 0 °C
Freezing point	: No data available
Boiling point/Boiling range	: > 100 °C
Flash point	: No data available
Autoignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: 1.13
Solubility	: Soluble in water.
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: 1300 – 3000 cP at 20 °C
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

### 9.2. Other information

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No additional information available

### 10.2. Chemical stability

Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

### 10.4. Conditions to avoid

No additional information available

### 10.5. Incompatible materials

Strong bases.

### 10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

# BREAKER

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### SECTION 11: Toxicological information

#### 11.1. Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified

#### Isotridecanol, ethoxylated (69011-36-5)

ATE CLP (oral)	500 mg/kg bodyweight
----------------	----------------------

#### Phosphoric Acid (7664-38-2)

LD50 oral rat	1530 mg/kg
ATE CLP (oral)	1530 mg/kg bodyweight

Skin corrosion/irritation	: Causes severe skin burns. pH: $\leq 1.5$
Serious eye damage/irritation	: Assumed to cause serious eye damage pH: $\leq 1.5$
Respiratory or skin sensitisation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Germ cell mutagenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Carcinogenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Reproductive toxicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
STOT-single exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met
STOT-repeated exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Aspiration hazard	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Potential adverse human health effects and symptoms	: Based on available data, the classification criteria are not met.

### SECTION 12: Ecological information

#### 12.1. Toxicity

Hazardous to the aquatic environment, short-term (acute)	: Not classified
Hazardous to the aquatic environment, long-term (chronic)	: Not classified

#### 12.2. Persistence and degradability

##### BREAKER

Persistence and degradability	Biodegradable. The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No. 648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.
-------------------------------	---

#### 12.3. Bioaccumulative potential

##### BREAKER

Bioaccumulative potential	No bioaccumulation.
---------------------------	---------------------

#### 12.4. Mobility in soil

No additional information available

# BREAKER

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

### 12.5. Results of PBT and vPvB assessment

#### BREAKER

This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII

This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

#### Component

Isotridecanol, ethoxylated (69011-36-5)

This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII  
This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

### 12.6. Other adverse effects

Additional information : Avoid release to the environment.

## SECTION 13: Disposal considerations




### 13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations.

Waste / unused products : Avoid release to the environment.

## SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

ADR	IMDG	IATA
<b>14.1. UN number</b>		
UN 3264	UN 3264	UN 3264
<b>14.2. UN proper shipping name</b>		
CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S.	CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S.	Corrosive liquid, acidic, inorganic, n.o.s.
<b>Transport document description</b>		
UN 3264 CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (Phosphoric Acid (21%)), 8, III, (E)	UN 3264 CORROSIVE LIQUID, ACIDIC, INORGANIC, N.O.S. (Phosphoric Acid (21%)), 8, III	UN 3264 Corrosive liquid, acidic, inorganic, n.o.s. (Phosphoric Acid (21%)), 8, III
<b>14.3. Transport hazard class(es)</b>		
8	8	8
		
<b>14.4. Packing group</b>		
III	III	III
<b>14.5. Environmental hazards</b>		
Dangerous for the environment : No	Dangerous for the environment : No Marine pollutant : No	Dangerous for the environment : No
No supplementary information available		

### 14.6. Special precautions for user

#### Overland transport

Classification code (ADR) : C1  
Special provisions (ADR) : 274  
Limited quantities (ADR) : 5I  
Packing instructions (ADR) : P001, IBC03, LP01, R001  
Mixed packing provisions (ADR) : MP19  
Portable tank and bulk container instructions (ADR) : T7  
Portable tank and bulk container special provisions (ADR) : TP1, TP28  
Tank code (ADR) : L4BN  
Vehicle for tank carriage : AT

# BREAKER

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Transport category (ADR) : 3  
Special provisions for carriage - Packages (ADR) : V12  
Hazard identification number (Kemler No.) : 80  
Orange plates :



Tunnel code : E  
EAC code : 2X  
APP code : B

### Transport by sea

Special provisions (IMDG) : 223, 274  
Limited quantities (IMDG) : 5 L  
Packing instructions (IMDG) : P001, LP01  
IBC packing instructions (IMDG) : IBC03

### Air transport

PCA Limited quantities (IATA) : Y841  
PCA limited quantity max net quantity (IATA) : 1L  
PCA packing instructions (IATA) : 852  
PCA max net quantity (IATA) : 5L  
CAO packing instructions (IATA) : 856  
CAO max net quantity (IATA) : 60L  
Special provisions (IATA) : A3, A803

### 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### 15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

Detergent Regulation (648/2004/EC): Labelling of contents:

Component	%
non-ionic surfactants	<5%

#### 15.1.2. National regulations

No additional information available

### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

## SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

### Full text of H- and EUH-statements:

Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Met. Corr. 1	Corrosive to metals, Category 1
Skin Corr. 1	Skin corrosion/irritation, Category 1

# BREAKER

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Skin Corr. 1B	Skin corrosion/irritation, Category 1, Sub-Category 1B
Skin Irrit. 2	Skin corrosion/irritation, Category 2
H290	May be corrosive to metals.
H302	Harmful if swallowed.
H314	Causes severe skin burns and eye damage.
H315	Causes skin irritation.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.

### Classification and procedure used to derive the classification for mixtures according to Regulation (EC) 1272/2008 [CLP]:

Skin Corr. 1	H314	On basis of test data
--------------	------	-----------------------

SDS EU (REACH Annex II)

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.