

Pan Head Pozidriv® Self Tapping Screw



DESCRIPTION

Pan Head Pozidriv® Stainless Steel Self Tapping Screws with good corrosion resistance. Designed for use with sheet metal. Suitable for outdoor use.

DISTINCTIVE FEATURES

- Self Tapping
- Pozidriv®
- Stainless Steel Grade A2 (304)
- Self-coloured Finish
- Corrosion Resistant
- Non-magnetic
- Dome head style
- No.4, No.6 and No.8 options
- Supplied in packs of 100

APPLICATIONS

Self Tapping stainless steel screws are widely used in many applications to secure two materials together. Suitable for outdoor use and where improved corrosion resistance is required. Typical applications include manufacturing, construction, joinery, maintenance and DIY tasks. Suitable for use in food, medical and non-severe chemical environments, and in both low and high temperature applications. Note: Not suitable for use with non-oxidising acids and agents or in chloride rich environments. These self tapping screws are designed for use with sheet metal and will require a pilot hole for this purpose. Pan head, self tapping screws are typically used for high torque applications into metal or wood and some plastics.

Pan Head

Self Tapping

Stainless Steel

Self Colour





GENERAL SPECIFICATION

Series	Self Tapping Screw
Type	PoziDriv®



MATERIALS

Material	Stainless Steel
Finish	Self Colour



CERTIFICATION AND STANDARDS

Material Specification	DIN 7981C ~ISO 7049
------------------------	---------------------





OPTIONS (MOQ may apply)

Lengths	Various
Thread Sizes	M1.6 to M12
Thread Type	Coarse and Fine
Material	Steel
Head Styles	e.g. Button, Cheese, Countersunk, Slotted



DIMENSIONS/DRAWINGS

Units	mm - unless stated otherwise
-------	------------------------------



Part number	Thread size	Material strength Rm (N/mm ²)	Sheet metal thickness (mm)															
			1.1	1.2	1.3	1.4	1.5	1.6	1.7	1.8	1.9	2.0	2.2	2.5	2.8	3.0	3.5	
33-7122	2.9	> 101	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.3				
33-7123		approx. 301	2.2	2.2	2.2	2.2	2.3	2.3	2.3	2.3	2.4	2.4	2.4					
33-7124		> 501	2.2	2.2	2.3	2.3	2.4	2.4	2.4	2.4	2.5	2.5	2.5					
33-7125	3.5	> 102			2.6	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.8	2.9			
33-7126		approx. 302			2.6	2.7	2.7	2.7	2.7	2.8	2.8	2.9	2.9	3.0	3.0			
33-7127		> 502			2.7	2.8	2.8	2.9	2.9	2.9	2.9	3.0	3.0	3.1	3.1			
33-7128		> 104				3.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.3	3.4	3.5	
33-7129	4.2	approx. 304				3.1	3.2	3.2	3.2	3.3	3.3	3.4	3.4	3.5	3.6	3.6	3.6	
33-7130		> 504				3.3	3.3	3.4	3.4	3.4	3.4	3.5	3.5	3.6	3.6	3.6	3.7	



PART NUMBER TABLE

Part number	A Thread size	B Length	C Screwdriver size	D Head width	E Head depth	UNSPSC	EAN	Country of Origin
33-7122	2.9	6.5	PZ1 - 2.9	5.6	2.20	73181900	5053556010356	China
33-7123		9.5				73181900	5053556010363	China
33-7124		13.0				73181900	5053556010370	China
33-7125	3.5	6.5	PZ2 – 3.9	6.9	2.6	73181900	5053556010387	China
33-7126		9.5				73181900	5053556010394	China
33-7127		13.0				73181900	5053556010400	China
33-7128		19.0				73181900	5053556010417	China
33-7129	4.2	13.0	PZ2 – 4.3	8.20	3.05	73181900	5053556010424	China
33-7130		19.0				73181900	5053556010431	China

For further information on pricing, delivery, and long-term stock agreements please get in touch with your local business development contact, telephone our main office on **01206 838000** or email **Sales@Rapidonline.com**.



Important Notice: This data sheet and its contents (the "Information") belong to Rapid Electronics Limited or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Rapid Electronics Limited assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Rapid Electronics Limited were aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict Rapid Electronics Limited's liability for death or personal injury resulting from its negligence.