

Safety Data Sheet (SDS) Report

Koolpak Ltd, Unit 5, Sterte Road Industrial Estate, 145 Sterte Road,

Poole, Dorset, BH15 2AF, UK 0800 180 4285

Number: SDS1301140003

Jan. 14, 2013

Issue Date:

Sample Description:

Application Received :

Applicant:

The sample information was submitted and identified on applicant's behalf to be:

January 14, 2013

Product Name : Instant Cold Pack

Application Reviewed : January 21, 2013

Service Requested:

As requested by the applicant, the Safety Data Sheet (SDS) was generated by the submitted information in accordance with Regulation (EC) No. 1907/2006, Regulation (EC) No 1272/2008, EU Commission Directive 67/548/EEC, 1999/45/EC, for details please refer to attached pages.

Authorized By:

On Behalf Of Regulatory Affairs in Intertek Testing Services Ltd., Shanghai (Suzhou Branch)

Deane You

Regulatory Consultant

This report shall not be reproduced except in full, without the written approval of the laboratory.

Intertek Testing Services Ltd., Shanghai (Suzhou Branch)

Building B, SIP Ecological Hub, 18 Zhanye Road, Suzhou Industrial Park, Jiangsu, China Tel: 0086-512-86668421 Fax: 0086-512-86668326 ZIP: 215121

SDS1301140003 Version:1.0

According to Regulation (EC) No. 453/2010

Issue Date: 2013-01-14

Product identifier

Trade name:	Instant Cold Pack
Proper shipping name:	None
Other identities:	No data available

1.2. Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses 1.2.1.

Used for human local cold compress.

1.2.2. **Uses advised against**

Advise against other uses.

1.3. Details of the supplier of the safety data sheet

Supplier:	Koolpak Ltd
Address:	Unit 5, Sterte Road Industrial Estate, 145 Sterte Road, Poole, Dorset, BH15 2AF, UK
Telephone:	0800 180 4285
Fax:	0870 622 1133
E-mail:	sales@koolpak.co.uk

Importer:	
Address:	
Telephone:	
E-mail:	

1.4. **Emergency telephone number**

Country	Advisory body	Address	Emergency number

SECTION 2: Hazards identification

Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008 [CLP]

Not classified.

Classification according to Directive 67/548/EEC or 1999/45/EC

Not classified.

Other adverse physicochemical, human health and environmental effects

No reliable data available.

Label elements

Labelling according to Regulation (EC) No 1272/2008 [CLP]

Not applicable.

Other hazards 2.3.

No reliable data available.

SECTION 3: Composition/information on ingredients

Substances

Not applicable.

3.2. **Mixtures**

Name	CAS No.	EC No.	Index No.	REACH No.	% wt/wt	Classification according to CLP	Classification according to DSD
Urea	57-13-6	200-315-5	-	-	50	Not classified	Not classified
Water	7732-18-5	231-791-2	-	-	50	Not classified	Not classified

According to Regulation (EC) No. 453/2010

SDS1301140003 Issue Date: 2013-01-14 Version:1.0

SECTION 4: First aid measures

Description of first aid measures

Inhalation: Move victim to fresh air. If not breathing, give artificial respiration. Get medical attention.

Skin contact: Immediately wash with plenty of soap and water. Get medical attention if irritation occurs.

Eye contact: Immediately flush eyes with running water for at least 20 minutes holding eyelids open. Get medical attention.

Ingestion: Do not induce vomiting. Give 1-2 glasses of water to a conscious victim. Never give anything by mouth to an unconscious victim. Get medical attention.

Notes to physician: Symptomatic treatment.

Most important symptoms and effects, both acute and delayed

No reliable data available.

4.3. Indication of any immediate medical attention and special treatment needed

No reliable data available.

SECTION 5: Firefighting measures

5.1. **Extinguishing media**

Foam.

Dry chemical powder.

Carbon dioxide.

Water spray or fog - large fires only.

Special hazards arising from the substance or mixture

Fire/explosion hazard: No data available.

Main combustion gas: No data available.

Advice for firefighters 5.3.

Alert Fire Brigade and tell them location and nature of hazard.

Wear breathing apparatus plus protective gloves.

Prevent, by any means available, spillage from entering drains or water courses.

Use water delivered as a fine spray to control fire and cool adjacent area.

DO NOT approach containers suspected to be hot.

Cool fire exposed containers with water spray from a protected location.

Only when safe to do so, remove containers from path of fire.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel 6.1.1.

Wear suitable protective equipment.

6.1.2. For emergency responders

Remove ignition sources and provision of sufficient ventilation, evacuate the danger area and consult experts.

6.2. **Environmental precautions**

Take precautions to prevent entry into waterways, sewers, or surface drainage systems. Dispose according to local or international regulations.

Methods and material for containment and cleaning up

Use appropriate tools to put the spilled solid in suitable container for recovery or disposal, avoid splashing.

Reference to other sections

Refer to Section 8 for Personal Protective Equipment advice.

SECTION 7: Handling and storage

Precautions for safe handling

Avoid ingestion, inhalation, skin and eye contact. Minimize spill and splashing. Handle in accordance with good industrial hygiene practice and any legal requirements.

Conditions for safe storage, including any incompatibilities

Suitable container: No data available. Check all containers are clearly labelled and free from leaks.

According to Regulation (EC) No. 453/2010

Issue Date: 2013-01-14 Version:1.0

Storage incompatibility: Avoid reaction with strong acid, alkali and oxidizing agents.

Specific end use(s)

Apart from the uses mentioned in section 1.2, no other specific uses are stipulated.

SECTION 8: Exposure controls/personal protection

Control parameters

At this time no TLV of this mixture has been established, even though this material may produce adverse health effects (as evidenced in animal experiments or clinical experience). Airborne concentrations must be maintained as low as practically possible and occupational exposure must be kept to a minimum.

8.2. **Exposure controls**

Appropriate engineering controls: Process enclosures, local exhaust ventilation, or other engineering controls to keep airborne levels below recommended exposure limits.

General Personal Protection: Safety goggles or face shield, protective chemical resistant gloves, protective clothing.

SECTION 9: Physical and chemical properties			
9.1. Information on basic physical and chemical properties			
Physical state:	No data available		
Colour:	No data available		
Odour:	No data available		
pH:	No data available		
Melting point/freezing point:	No data available		
Boiling point:	No data available		
Flash point:	No data available		
Vapour pressure:	No data available		
Relative density:	No data available		
Water solubility:	No data available		
Partition coefficient (n-octanol/water):	No data available		
Auto-ignition temperature:	No data available		
Flammability:	No data available		
Upper/lower flammability limits:	No data available		
Upper/lower explosive limits:	No data available		
Explosive properties:	No data available		
Oxidising properties:	No data available		
Dissociation constants:	No data available		
Surface tension:	No data available		
Viscosity:	No data available		

Other information

No data available.

SECTION 10: Stability and reactivity

Reactivity

May react with strong acid, alkali, oxidizing agents and incompatible materials.

10.2. **Chemical stability**

Stable under normal condition.

10.3. Possibility of hazardous reactions

Hazardous reactions may occur if contact with incompatible material.

Conditions to avoid 10.4.

High temperature, ignition sources (sparks, flames, static), incompatible materials.

SDS1301140003

According to Regulation (EC) No. 453/2010 SDS1301140003 Issue Date : 2013-01-14 Version:1.0

Incompatible materials

Strong acid, alkali and oxidizing agents.

Hazardous decomposition products

On combustion or thermal decomposition, may emit toxic fumes.

SECTION 11: Toxicological information

Information on toxicological effects

Acute toxicity:	No data available	
Skin corrosion/irritation:	Urea Cas No.: 57-13-6	
	Not irritating (OECD Guideline 404)	
Serious eye damage/irritation:	Urea Cas No.: 57-13-6	
	Not irritating (OECD Guideline 404)	
Respiratory or skin sensitisation:	No data available	
Germ cell mutagenicity:	No data available	
Carcinogenicity:	No data available	
Reproductive toxicity:	No data available	
STOT-single exposure:	No data available	
STOT-repeated exposure:	Urea Cas No.: 57-13-6	
	Dermal: No dose-dependent toxicity observed.(conc. level: 40% ointment)	
Aspiration hazard:	No data available	

SECTION 12: Ecological information

12.1. **Aquatic toxicity**

Acute (short-term) toxicity:	Urea Cas No.: 57-13-6
	Crustaceans (Daphnia Magna, 24h): EC50 > 10000 mg/L (DIN 38412 Teil 11 (modified))
	Algae/aquatic plants (Pseudomonas putida and Entosiphon sulcatum, 72h): Toxicity threshold=
	29 mg/L
Chronic (long-term) toxicity:	No data available

12.2. Persistence and degradability

Biodegradation:	No data available
Abiotic degradation:	No data available

12.3. **Bioaccumulative potential**

Bioconcentration factor (BCF): No data avail	ilable
--	--------

12.4. Mobility in soil	
Known or predicted distribution to	No data available
environmental compartments:	
Adsorption/Desorption:	Urea Cas No.: 57-13-6
	Urea adsorption by the soil increased with increasing concentration of added urea-N and
	adsorption coefficients ranged from 0.037 to 0.064.
	Known or predicted distribution to environmental compartments:

12.5. Results of PBT and vPvB assessment

No data available.

Other adverse effects

No data available.

SECTION 13: Disposal considerations

Waste treatment methods

Product disposal: refer to specific national regulation.

Contaminated packaging: contaminated, empty containers must be disposed of as chemical waste.

SECTION 14: Transport information

Based on available data, the information according to UN recommendation on the transport of dangerous goods is given as below:

SDS1301140003 Version:1.0

According to Regulation (EC) No. 453/2010 Issue Date: 2013-01-14

Land transp	ort (ADR / RID / GGVSE)
-------------	-------------------------

14.1 UN number	None	14.4 Packing group	None	
14.2 UN proper shipping	None	14.5 Environmental hazards	No relevant data	
name			Hazard identification (Kemler)	None
14.3 Transport hazard	None	14.6 Special precautions for user	Classification Code	None
class(es)			Hazard Label	None
	usci	Special provisions	None	
			Add limited quantity	None

Air transport (ICAO-IATA / DGR)

14.1 UN number	None	14.4 Packing group	None	
14.2 UN proper shipping	None	14.5 Environmental hazards	No relevant data	
name			Special provisions	None
14.3 Transport hazard class(es)	None		Cargo Only Packing Instructions	None
Class(es)		Cargo Only Maximum Qty / Pack	None	
		14.6 Special precautions for user	Passenger and Cargo Packing Instructions	None
			Passenger and Cargo Maximum Qty / Pack	None
			Passenger and Cargo Limited Quantity Packing Instructions	None
			Passenger and Cargo Maximum Qty / Pack	None

Sea transport (IMDG-Code / GGVSee)

14.1 UN number	None	14.4 Packing group		
14.2 UN proper shipping	None	14.5 Environmental hazards	No data available	
name			EMS number	None
		14.6 Special precautions for user	Special provisions	None
14.3 Transport hazard	None		Limited quantities	None
class(es)				

Inland waterways transport (ADNR / River Rhine)

14.1 UN number	None	14.4 Packing group	None	
14.2 UN proper shipping	None	14.5 Environmental hazards	No relevant data	
name			Classification code	None
14.3 Transport hazard	None	14.6 Special precautions for user	Limited quantity	None
class(es)			Equipment required	None
			Fire cones number	None

14.7. Transport in bulk according to Annex II of MARPOL 73 / 78 and the IBC Code

No data available.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

This safety data sheet is in compliance with the following EU legislation and its adaptations - as far as applicable - 67/548/EEC, 1999/45/EC, Regulation (EC) No 1272/2008, Regulation (EC) No 1907/2006, 98/24/EC, 92/85/EEC, 94/33/EC, 91/689/EEC and 1999/13/EC.

15.1.2. International/national regulations

UN recommendation on the transport of dangerous goods

15.2. Chemical safety assessment

No chemical safety assessment has been carried out for the mixture by the supplier.

Safety Data Sheet

According to Regulation (EC) No. 453/2010

SDS1301140003 Issue Date: 2013-01-14 Version:1.0

SECTION 16: Other information 16.1 Indication of changes Version No. Change date Change description No data available No data available No data available

16.2 Key literature references and sources for data

- ESIS (European chemical Substances Information System), http://esis.jrc.ec.europa.eu/
- REACH registered chemicals, http://echa.europa.eu/chem_data_en.asp
- IFA GESTIS International limit values for chemical agents Occupational exposure limits (OELs), http://www.dguv.de/ifa/en/gestis/limit_values/index.jsp

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation. Many factors determine whether the reported Hazards are Risks in the workplace or other settings. Risks may be determined by reference to Exposures Scenarios. Scale of use, frequency of use and current or available engineering controls must be considered.

The information presented in this SDS is based on our current knowledge and available data as of the issue date, and is only intended to describe the product for the purposes of protecting human health and environment from potential hazard. It should not therefore be construed as guaranteeing any specific property of the product.