

**Technical Data Sheet** 

# LOCTITE<sup>®</sup> 4090™

July 2014

#### PRODUCT DESCRIPTION

 $\text{LOCTITE}^{\textcircled{8}}$  4090<sup>TM</sup> provides the following product characteristics:

Technology	Cyanoacrylate / Epoxy Hybrid				
Chemical Type (Part A)	Cyanoacrylate				
Chemical Type (Part B)	Ероху				
Appearance (Comp. A)	Transparent colorless to straw colored liquid <sup>LMS</sup>				
Appearance (Comp. B)	Off-white to light yellow gel <sup>LMS</sup>				
Appearance (Mixture)	Clear to slightly cloudy gel				
Components	Two component - requires mixing				
Mix Ratio, by volume - Part A: Part B	1:1				
Viscosity	High				
Cure	Room temperature cure after mixing				
Application	Bonding				

LOCTITE<sup>®</sup> 4090<sup>™</sup> is a two component, general purpose adhesive which provides a very fast fixture at room temperature. It is designed to bond a variety of substrates including metals, most plastics and rubbers. LOCTITE<sup>®</sup> 4090<sup>™</sup> provides good temperature and moisture resistance which also makes it suitable for applications in high temperature/humidity environments. The thixotropic nature makes it suitable for applications where good gap filling properties on rough and poorly fitting surfaces are required.

#### TYPICAL PROPERTIES OF UNCURED MATERIAL Part A:

Specific Gravity, g/cm <sup>3</sup>	1.01
Viscosity, Cone & Plate, mPa·s (cP):	
Temperature: 25 °C	4,000 to 7,000 <sup>LMS</sup>
Flash Point - See SDS	
Part B:	
Specific Gravity, g/cm <sup>3</sup>	1.06
Viscosity, Cone & Plate, mPa·s (cP):	
Temperature: 25 °C	25,000 to 40,000 <sup>LMS</sup>
Flash Point - See SDS	

#### **TYPICAL CURING PERFORMANCE**

Curing is initiated on mixing the Part A and Part B components. Handling strength is achieved rapidly; full strength is achieved over time.


# **Fixture Time**

Fixture time is defined as the time to develop a shear strength of 0.1  $\ensuremath{\text{N/mm^2}}$  .

Fixture Time @ 25°C, seconds <180<sup>LMS</sup>


#### Cure Speed vs. Substrate

The rate of cure will depend on the substrate used. The graph below shows the shear strength developed with time on steel lap shears compared to different materials and tested according to ISO 4587.



#### Cure Speed vs. Bond Gap


The rate of cure will depend on the bondline gap. The following graph shows the shear strength developed with time on grit blasted mild steel lap shears at different controlled gaps and tested according to ISO 4587.



#### Cure Speed vs. Temperature

The rate of cure will depend on the ambient temperature. The graph below shows the shear strength developed with time at different temperatures on grit blasted mild steel lap shears and tested according to ISO 4587.





# TYPICAL PROPERTIES OF CURED MATERIAL

Cured for 1 week @ 22 °C		
Physical Properties:		
Glass Transition Temperature, ISO 11359-	2, °C 88	5
Coefficient of Thermal Expansion, ISO 113	359-2 K <sup>-1</sup> :	
Below Tg (88°C)		71×10 <sup>-06</sup>
Above Tg (88°C)		175×10 <sup>-06</sup>
Shore Hardness, ISO 868, Durometer D	65	to 69
Tensile Strength, at break, ISO 527-3	N/mm <sup>2</sup>	7.1
	(psi)	(1,025)
Tensile Modulus, ISO 527-3	N/mm²	000
	(psi)	(81,800)
Elongation, at break, ISO 527-3, %	3.	6

#### TYPICAL PERFORMANCE OF CURED MATERIAL Adhesive Properties


Cured for 168 hours @ 22 °C

Shea	ar St	rengt	h,	Lap	Shear Strength,	ISO	4587:	
~				• •			•	


Steel (grit blasted)	N/mm² 17
	(psi) (2,420)
Aluminum	N/mm² 7.6
	(psi) (1,100)
Aluminum (etched)	N/mm² 13
	(psi) (1,900)
Zinc dichromate	N/mm <sup>2</sup> 9.1
	(psi) (1,320)
Stainless steel	N/mm² 15
	(psi) (2,120)
ABS	N/mm <sup>2</sup> 5.2
	(psi) (750)
Phenolic	N/mm <sup>2</sup> 3.2
	(psi) (460)
Polycarbonate	N/mm <sup>2</sup> 6.9
-	(psi) (1,000)
Nitrile	N/mm² 0.7
	(psi) (100)
Wood (Oak)	N/mm² 4.8
	(psi) (700)
Epoxy	N/mm <sup>2</sup> 9.1
	(psi) (1,320)
Polyethylene	N/mm² 0.5
	(psi) (72)
Polypropylene	N/mm <sup>2</sup> 0.6
	(psi) (87)


# TYPICAL ENVIRONMENTAL RESISTANCE

Cured for 1 week @ 22 °C Lap Shear Strength, ISO 4587: Steel (grit blasted)



# Heat Aging





# **Chemical/Solvent Resistance**

Aged under conditions indicated and tested @ 22 °C.

		% of initial strength			
Environment	°C	100 h	500 h	1000 h	
Water	22	90	75	70	
Water	60	80	55	55	
Motor oil	40	120	130	130	
Unleaded gasoline	22	95	100	105	
Ethanol	22	85	90	90	
Isopropanol	22	100	100	95	
Water/glycol 50/50	87	50	5	5	
98% RH	40	85	70	70	
95% RH	65	95	85	65	

Lap Shear Strength, ISO 4587: Polycarbonate

		% of initial strength			
Environment	°C	100 h	500 h	1000 h	
98% RH	40	100	90	80	

Lap Shear Strength, ISO 4587:

Aluminum

		% of initial strength		
Environment	°C	100 h	300 h	500 h
95% RH	65	100	95	85

#### **GENERAL INFORMATION**

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

For safe handling information on this product, consult the Safety Data Sheet (SDS).

Where aqueous washing systems are used to clean the surfaces before bonding, it is important to check for compatibility of the washing solution with the adhesive. In some cases these aqueous washes can affect the cure and performance of the adhesive.

#### Directions for use:

- 1. Bond areas should be clean and free from grease. Clean all surfaces with a Loctite<sup>®</sup> cleaning solvent and allow to dry.
- 2. To use, Part A and Part B must be blended. Product can be applied directly from dual cartridge by dispensing through the mixer head supplied.
- 3. Position dual cartridge upright for 1 minute. In this upright position, insert the cartridge into the application gun and start the plunger into the cylinders using light pressure on the trigger.
- 4. Remove the cartridge cap and expel a small amount of adhesive to be sure both sides are flowing evenly and freely. Attach the static mixing nozzle to the end of the cartridge and begin dispensing the adhesive. .
- 5. Purge and dispose of the first 3 8 cm from the end of the mix nozzle, as it may not be sufficiently mixed.
- 6. Apply the mixed adhesive to one of the bond surfaces to be joined. Parts should be assembled immediately after the mixed adhesive has been applied.
- 7. Bonds should be held fixed or clamped until adhesive has fixtured.
- 8. Keep assembled parts from moving during cure. The bond should be allowed to develop full strength before subjecting to any service load.

### Loctite Material Specification<sup>LMS</sup>

LMS dated May 27, 2013 (Part A) and LMS dated June 10, 2013 (Part B). Test reports for each batch are available for the indicated properties. LMS test reports include selected QC test parameters considered appropriate to specifications for customer use. Additionally, comprehensive controls are in place to assure product quality and consistency. Special customer specification requirements may be coordinated through Henkel Loctite Quality.

#### Storage

Store product in the unopened container in a dry location. Storage information may be indicated on the product container labeling.

Optimal Storage: 2 °C to 8 °C. Storage below 2 °C or greater than 8 °C can adversely affect product properties. Material removed from containers may be contaminated during use. Do not return product to the original container. Henkel Corporation cannot assume responsibility for product which has been contaminated or stored under conditions other than those previously indicated. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

#### Conversions

(°C x 1.8) + 32 = °F kV/mm x 25.4 = V/mil mm / 25.4 = inches  $\mu m / 25.4 = mil$  $N \ge 0.225 = Ib$ N/mm x 5.71 = lb/in N/mm<sup>2</sup> x 145 = psi MPa x 145 = psi N·m x 8.851 = lb·in  $N \cdot m \ge 0.738 = Ib \cdot ft$ N·mm x 0.142 =  $oz \cdot in$ mPa·s = cP

#### Note:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. The product can have a variety of different applications as well as differing application and working conditions in your environment that are beyond our control. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal injury caused by our negligence and any liability under any applicable mandatory product liability law.

#### In case products are delivered by Henkel Belgium NV, Henkel Electronic Materials NV, Henkel Nederland BV, Henkel Technologies France SAS and Henkel France SA please additionally note the following:

In case Henkel would be nevertheless held liable, on whatever legal ground, Henkel's liability will in no event exceed the amount of the concerned delivery.

#### In case products are delivered by Henkel Colombiana, S.A.S. the following disclaimer is applicable:

The information provided in this Technical Data Sheet (TDS) including the recommendations for use and application of the product are based on our knowledge and experience of the product as at the date of this TDS. Henkel is, therefore, not liable for the suitability of our product for the production processes and conditions in respect of which you use them, as well as the intended applications and results. We strongly recommend that you carry out your own prior trials to confirm such suitability of our product.

Any liability in respect of the information in the Technical Data Sheet or any other written or oral recommendation(s) regarding the concerned product is excluded, except if otherwise explicitly agreed and except in relation to death or personal

Henkel Europe Henkel Asia Pacific +49.89.320800.1800 +86.21.2891.8859 For the most direct access to local sales and technical support visit: www.henkel.com/industrial

injury caused by our negligence and any liability under any applicable mandatory product liability law.

# In case products are delivered by Henkel Corporation, Resin Technology Group, Inc., or Henkel Canada Corporation, the following disclaimer is applicable:

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits. The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

#### Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. <sup>®</sup> denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.1