



## Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 8

TEROSON MS 9360 BK

SDS No. : 522589  
V001.5

Revision: 04.08.2016

printing date: 12.07.2018

Replaces version from: 29.07.2016

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

TEROSON MS 9360 BK

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

MS Adhesive

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000

Fax-no.: +44 1442 278071

ua-productsafety.uk@uk.henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.2. Label elements

##### Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

**General chemical description:**

adhesive and sealant

**Base substances of preparation:**

Polyether

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Contains no dangerous substances exceeding the limits of the EU-Regulation

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

**Inhalation:**

Move to fresh air, consult doctor if complaint persists.

**Skin contact:**

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

**Eye contact:**

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

**Ingestion:**

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

#### 4.2. Most important symptoms and effects, both acute and delayed

No data available.

#### 4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

**Suitable extinguishing media:**

All common extinguishing agents are suitable.

**Extinguishing media which must not be used for safety reasons:**

High pressure waterjet

#### 5.2. Special hazards arising from the substance or mixture

In case of fire toxic gases can be released.

#### 5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Wear protective equipment.

### SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

Wear protective equipment.

#### 6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

**6.3. Methods and material for containment and cleaning up**

Remove mechanically.

Dispose of contaminated material as waste according to Section 13.

**6.4. Reference to other sections**

See advice in section 8

**SECTION 7: Handling and storage**

**7.1. Precautions for safe handling**

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

**7.2. Conditions for safe storage, including any incompatibilities**

Ensure good ventilation/extraction.

Storage at 5 to 25°C is recommended.

Store in a cool, frost-free place.

**7.3. Specific end use(s)**

MS Adhesive

<b>SECTION 8: Exposure controls/personal protection</b>
---

**8.1. Control parameters****Occupational Exposure Limits**Valid for  
Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [LIMESTONE, RESPIRABLE MARBLE, RESPIRABLE]		4	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [LIMESTONE, TOTAL INHALABLE MARBLE, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		EH40 WEL
Carbon black 1333-86-4 [CARBON BLACK]		7	Short Term Exposure Limit (STEL):		EH40 WEL
Carbon black 1333-86-4 [CARBON BLACK]		3,5	Time Weighted Average (TWA):		EH40 WEL

**Occupational Exposure Limits**Valid for  
Ireland

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		IR_OEL
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, TOTAL INHALABLE DUST]		10	Time Weighted Average (TWA):		IR_OEL
Carbon black 1333-86-4 [CARBON BLACK]		3,5	Time Weighted Average (TWA):		IR_OEL
Carbon black 1333-86-4 [CARBON BLACK]		7	Short Term Exposure Limit (STEL):		IR_OEL

**Biological Exposure Indices:**

None

**8.2. Exposure controls:**Engineering controls:  
Ensure good ventilation/extraction.

**Respiratory protection:**

In case of dust formation, we recommend wearing of appropriate respiratory protection equipment with particle filter P (EN 14387).

This recommendation should be matched to local conditions.

**Hand protection:**

Chemical-resistant protective gloves (EN 374). Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374): Polychloroprene (CR;  $\geq$  1 mm thickness) or natural rubber (NR;  $\geq$  1 mm thickness) Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374): Polychloroprene (CR;  $\geq$  1 mm thickness) or natural rubber (NR;  $\geq$  1 mm thickness) This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

**Eye protection:**

Protective goggles

Protective eye equipment should conform to EN166.

**Skin protection:**

Wear protective equipment.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

**Advices to personal protection equipment:**

Use only personal protection that's CE-labelled according to Directive 89/686/EEC (Europe) or to Regulation No. 819 of 19 August 1994 (Norway).

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Appearance	paste pasty black
Odor	characteristic
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density (20 °C (68 °F))	1,37 g/cm <sup>3</sup>
Bulk density	No data available / Not applicable
Viscosity (; 20 °C (68 °F); Conc.: 100 % product)	200 - 300 pa.s
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative) (20 °C (68 °F); Solvent: Water)	Insoluble
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

## 9.2. Other information

No data available / Not applicable

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

None if used for intended purpose.

### 10.2. Chemical stability

Stable under recommended storage conditions.

### 10.3. Possibility of hazardous reactions

See section reactivity

### 10.4. Conditions to avoid

None if used for intended purpose.

### 10.5. Incompatible materials

None if used properly.

### 10.6. Hazardous decomposition products

No decomposition if used according to specifications.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

#### General toxicological information:

To the best of our knowledge no harmful effects are to be expected if the product is handled and used properly.

## SECTION 12: Ecological information

#### General ecological information:

Do not empty into drains, soil or bodies of water.

### 12.1. Toxicity

No data available.

### 12.2. Persistence and degradability

No data available.

### 12.3. Bioaccumulative potential / 12.4. Mobility in soil

No data available.

### 12.5. Results of PBT and vPvB assessment

No data available.

### 12.6. Other adverse effects

No data available.

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

Product disposal:

In consultation with the responsible local authority, must be subjected to special treatment.

Waste code

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

08 04 10 Waste adhesives and sealants other than those mentioned in 08 04 09.

### SECTION 14: Transport information

#### 14.1. UN number

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.4. Packing group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content 0 %  
(VOCV 814.018 VOC regulation  
CH)

#### 15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

---

<b>SECTION 16: Other information</b>
--------------------------------------

**Further information:**

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**