BFC2 808

RoHS



Vishay BCcomponents

Ø 10 mm Film Dielectric Trimmers



FEATURES

- Housing diameter 10 mm
- For a basic grid of 2.54 mm (0.1") or 2.50 mm
- Top and bottom or top adjustment
- Round head
- · Mounting: radial
- Mounting. rulati
 COMPLIANT
 Material categorization: for definitions of
 compliance please see <u>www.vishay.com/doc?99912</u>

APPLICATIONS

- Antennas
- Impedance matching circuits
- Medical
- RF
- For consumer and industrial equipment

QUICK REFERENCE DATA					
Rated DC voltage		150 V _{DC}			
Test DC voltage for 1 min		300 V _{DC}			
Maximum contact resistance		10 mΩ			
Minimum insulation resistance		10 000 MΩ			
	PP	-40 °C to +70 °C			
Category temperature range	PTFE	-40 °C to +85 °C			
	PP	40/070/21			
Climatic category (IEC 60068)	PTFE	40/085/21			
Minimum storage temperature		-55 °C			
Related specification		IEC 60418-1 and 4			
Effective angle of rotation		180° (rotation in 180° only, see "Life of trimmer")			
Operating torque		2 mNm to 25 mNm			
Maximum axial thrust		2 N			
Capacitance range (C _{min.} / C _{max.})		2.5 pF / 15 pF to 5.5 pF / 65 pF			
Life of trimmer		Maximum 10 cycles: rotation in 180° only (the electrical and mechanical performance is not guaranteed if rotated beyond 10 cycles)			
Quality level		Sampling and data evaluation for quality level in accordance with "MIL-STD-105D" and "IEC 60410":			
		< 0.15 % major defects < 0.65 % minor defects			
		Each capacitor is tested for minimum $C_{\mbox{max.}}$ and is also subjected to the full test voltage.			


1

BFC2 808

Vishay BCcomponents

VISHAY. www.vishay.com

DIMENSIONS in millimeters








FIG. 2



Trimmers BFC2 808 series




 0.6 ± 0.1

R = Rotor, S = Stator

The large hole is for bottom adjustment and the diameter is determined by user's requirements.

0.5 ± 0.15

Hole pattern



R = Rotor, S = Stator

2


BFC2 808



Vishay BCcomponents

ADJUSTMENT

For top adjustment a screwdriver or trimming key can be used; for bottom adjustment a key is required as shown below.



Bottom adjustment key

ORDERING INFORMATION							
	CATALOG NUMBER BFC2 808						
C _{min.} / C _{max.} (pF)	HOLE PATTERN 5 mm x 10 mm	ATTERN x 5 mm					
(pr)	ROUND HEAD	ROUND HEAD	ROUND HEAD				
	TOP AND BOTTO	TOP ADJUSTMENT					
2.5 / 15	31159	32159	-				
3 / 22.5	31229	32229	-				
5.5 / 40	31409	32409	-				
5.5 / 50	01029	01006	-				
5.5 / 65	31659	32659	01001				

MOUNTING

The trimmer can be mounted on printed-circuit boards with a grid of 2.50 mm or 2.54 mm and a minimum hole diameter of 1.25 mm.

PACKAGING

Bulk packaged in cardboard boxes lined with expanded plastic. For smallest packaging quantities (SPQ) see "Electrical Data" table.

ELECTRICAL DATA																			
		НАРЕ			tan δ AT C _{max.} x 10 ⁻⁴		TEMP.	MIN. f _{res}	COL.	SP	CATALOG								
MIN. C _{max.} OF AT 200 kHz HEAD (pF)	OF HEAD	FIG.	ADJ. MODE	DIEL.	1 MHz	100 MHz	COEFF. (10 ⁻⁶ /K)	AT C _{max.} (MHz)	OF BASE	Q	NUMBER BFC2								
2.5 / 15	Round	nd 1	Top + bottom	PP	< 10	≤ 25	-200 ± 700	420	Blue	800	808 31159								
2.57 15	nounu	2	TOP + DOLLOIN		<u> </u>	<u>≤</u> 25	-200 ± 700	420	Dide	800	808 32159								
3 / 22.5	Round	1	Top + bottom	PP	< 10	≤ 25	-200 ± 700	200	Green	800	808 31229								
5722.5	nounu	nound	nound	nounu	nouna	riouna	nouna	riound	2	2	Top T Bottom		_ 10	_ 20	200 ± 700	200	Green	800	808 32229
5.5 / 40	Round	1	Top + bottom Pl	PP	≤ 10	≤ 25	-200 ± 400	200	Grey	800	808 31409								
5.5740	nounu	2	TOP + DOLLOIN	ГГ	≤ 10	≥ 25	-200 ± 400	200	Grey	800	808 32409								
5.5 / 50	Round	1	Top + bottom	PTFE		< 05	-200 ± 400	170	Yellow	800	808 01029								
5.57 50	nouria	2	TOP + DOLLOIN	PIFE	FIFE		$PTFE \leq 10 \qquad \leq 25$	-200 ± 400	170	reliow	800	808 01006							
	Round	2	Тор							800	808 01001								
5.5 / 65	Round	1	Top bottom	PP	≤ 10	≤ 25	-200 ± 500	170	Yellow	800	808 31659								
	Round	2	Top + bottom								800	808 32659							

SOLDERING CONDITIONS

For general soldering conditions and wave soldering profile, we refer to the application note "Soldering Guidelines for Film Capacitors": <u>www.vishay.com/doc?28171</u>

Revision: 04-Aug-15





www.v	isha	y.com	

TEST PF	ROCEDUR	ES AND REQUIREMENT	<u>s</u>	
IEC 60418-1 CLAUSE	IEC 60068 TEST METHOD	TEST	PROCEDURE	REQUIREMENTS
4.2		Method of mounting	Method A	
14		Capacitance drift	After TC measurement	Δ C/C: \leq 4.5 % for C _{max.} $<$ 40 pF; Δ C/C: \leq 2.5 % for C _{max.} \geq 40 pF
19		Thrust	Axial thrust of 2 N	$\Delta C/C: \leq 0.3 \%$
21		Robustness of terminations:		
21.1	Ua	Tensile	1 N	No damage
21.2	Ub	Bending	1 cycle	No damage
22	Na	Rapid change of temperature	1 cycle; 0.5 h at lower and 0.5 h	∆C/C: ≤ 1.5 %
23	Т	Soldering:	at upper category temperature	
	Та	Solderability	Solder bath immersion 3 mm; 235 °C; 2 s	Good wetting, no mechanical damage
	Tb	Resistance to heat	Solder bath: 260 °C; 10 s	No mechanical damage
24	Eb	Impact bump	4000 ± 10 bumps; 40 g; 6 ms	Δ C/C: \leq 0.4 %; no mechanical damage
25	Fc	Vibration	Frequency 10 Hz to 55 Hz; amplitude 0.35 mm; 1.5 h	Δ C/C: \leq 0.8 %; no mechanical damage
26		Climatic sequence:		$\begin{array}{l} \Delta C/C:\leq 3 \ \% \ for \ C_{max.} < 80 \ pF; \\ \Delta C/C:\leq 6 \ \% \ for \ C_{max.} \geq 80 \ pF \end{array}$
26.1	В	Dry heat	16 h at upper category temperature	$\begin{array}{l} \mbox{tan } \delta : \leq 15 \mbox{ x } 10^{-4} \mbox{ for } C_{max.} < 80 \mbox{ pF}; \\ \mbox{tan } \delta : \leq 80 \mbox{ x } 10^{-4} \mbox{ for } C_{max.} \geq 80 \mbox{ pF} \end{array}$
				$\begin{array}{l} R_{ins.}: \geq 10 \; 000 \; M\Omega; \\ rotor \; contact \; R: \leq 10 \; \Omega \end{array}$
26.2	D	Damp heat accelerated, first cycle	1 cycle; 24 h; +40 °C; 95 % to 100 % RH	Voltage proof: 300 V for 1 min
26.3	Aa	Cold	16 h; -40 °C	Visual examination: no mechanical damage
26.5		Damp heat accelerated, remaining cycles	1 cycle; 24 h; +40 °C; 95 % to 100 % RH	Operating torque: 2 mNm to 35 mNm
27	Ca	Damp heat steady state	21 days; +40 °C; 90 % to 95 % RH	$ \begin{array}{l} \Delta C/C: \\ \leq 3 \ \% \ for \ C_{max.} < 100 \ pF; \\ \leq 3 \ \% \ for \ C_{max.} \geq 100 \ pF \end{array} $
			tan δ : \leq 20 x 10^{-4} for $C_{max.}$ $<$ 80 pF; tan δ : \leq 80 x 10^{-4} for $C_{max.}$ \geq 80 pF	
			$\begin{array}{l} R_{ins.}:\geq 10\;000\;M\Omega;\\ rotor\;contact\;R:\leq 10\;m\Omega \end{array}$	
				Voltage proof: 300 V for 1 min
				Visual examination: no mechanical damage
29		Mechanical endurance	10 cycles	Operating torque: 2 mNm to 35 mNm Δ C/C: \leq 1 %
			Maximum 10 cycles: rotation in 180° only (the electrical and	Δ C/C after axial thrust: \leq 0.4 %; rotor contact R: \leq 10 m Ω
			mechanical performance is not guaranteed if rotated beyond 10 cycles)	Voltage proof: 300 V for 1 min
				Visual examination: no mechanical damage
				Operating torque: 1.5 mNm to 37 mNr

Document Number: 28528

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.