

KLSH blade holder, left, with clamping element

For holding cutting inserts, no. 17710-17717



Application:

For cutting off and plunging with cutting inserts with no. 17710-17717.

Version:

- Precision-machined steel holder, burnished and hardened

Advantage:

- High-quality, hard-wearing steel holder with high-strength clamping element
- Precision-machined plate seat



Art. no.	17707 316
Width of cutting edge	3.1 mm
Shaft height	16 mm
Shank width	10 mm
Programming size	8 mm
Programming size 2	28 mm
Length	110 mm
Immersion depth	33 mm
Max. diameter	44 mm
Tool design	Left