

Tap wrench Basic

For holding square-head screw taps and reamers in accordance with DIN 10

ORION[®]

Application:

For holding square-head screw taps in accordance with DIN 10, reamers, screw extractors, screw tap extensions, tools with square mounts

Version:

- Housing, size 0-5, made of die-cast zinc, zinc-plated arm with knurling for medium loads

Advantage:

- Die-cast zinc ensures excellent value for money
- Ground and hardened steel jaws



Art. no.	13549 050
Tap wrench size	5
Suitable for min./max. square socket size	7-20 mm
Min./max. reamer cutting range	9-26 mm
Min./max. thread-cutting area, metric	12-33 mm
Length	700 mm

EAN-Code

4039247076697