

Micrometer heads

Robust design, with clamping nut

Mitutoyo

Application:

For installation in measuring instruments and presetters, as a setting and control element on machine tools, for fine adjustment of cross tables



Execution:

- With regular gradation
- With clamping nut
- Rotating spindle

Art. no.	32016 988
Brand	MITUTOYO
Manufacturer Part Number	151-221
Display	Nonius
Min./max. length measuring range	0-25 mm
Scale value	0.001 mm
Measuring surface diameter	8 mm
Measuring arrangement	Flat
Clamp in shank diameter	12 mm
Clamping shank length	25 mm
Coupling design	Slide coupling
Measuring spindle increments	0.5 mm
Spindle clamping	No
Design	Metric
Calibration Group	DE
Gross Weight	0.187 kg
Product Group	3MA

EAN

494636802229 1