

## G-COIL INSTALLATION APPLIANCE

### Description

Setting device for a G-COIL thread inser



### Characteristics

| Ref.   | EAN           | Threading diameter | Thread-cutting pitch |
|--------|---------------|--------------------|----------------------|
| 869316 | 3660338230677 | M2,5               | 0,45                 |
| 869317 | 3660338230684 | M3                 | 0,5                  |
| 869318 | 3660338230691 |                    |                      |
| 869319 | 3660338230707 |                    |                      |
| 869320 | 3660338230714 |                    |                      |
| 869321 | 3660338230721 | M7                 | 1                    |
| 869322 | 3660338230738 | M8                 | 1                    |
| 869323 | 3660338230745 | M8                 | 1,25                 |
| 869324 | 3660338230752 | M10                | 1                    |
| 869325 | 3660338230769 | M10                | 1,25                 |
| 869326 | 3660338230776 | M10                | 1,5                  |
| 869327 | 3660338230783 | M11                | 1,5                  |
| 869328 | 3660338230790 | M12                | 1                    |
| 869329 | 3660338230806 | M12                | 1,25                 |
| 869330 | 3660338230813 | M12                | 1,5                  |
| 869331 | 3660338230820 | M12                | 1,75                 |