

NC machine reamer, solid carbide

For universal use up to 1300 N/mm²

ATORN[®]



Application

For producing H7 fit tolerances in through holes on an NC machine in material groups up to 1300 N/mm².

Version

- 7-8° left-hand spiral and variable pitch, cemented carbide quality K10

Advantage

- good bore hole quality (dimensional tolerance, roundness, surface quality)

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GjMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	18	15	12	10	8	20	20	20	20	18	16	18		12	8	8	6		

Art. No.	11770 080
Cutting material	VHM
Groove type	Left-hand twist, 7-8°
Tool holding device	HA parallel shank
Cutting edge diameter	8 mm
Tolerance of fit	H7
Length	117 mm
Cutting edge length	32 mm
Shaft diameter	8 mm
Number of cutting edges	6 PCS
f steel 1300	0.12 mm/U
DIN	Similar to 8093

EAN-Code

4050293 129038