

**BOURNS**<sup>®</sup>**Multifuse**<sup>®</sup>

Resettable Fuses

**MF-RG model series**

1200 Columbia Ave.

Riverside, CA 92507

Phone : (951) 781-5500

Fax : (951) 781-5006

Resettable Overcurrent Protector



Preliminary spec

**Device Specification Sheet****Power Rating:**Max. Operating Voltage : 16 V<sub>dc</sub>

Max. Operating Current : 100 A

Working Temperature : -40 ~ 85 °C

Part feature &amp; marking(example):



Part No.	Dimension (mm)					
	A (Max)	B (Max)	C (Nom)	D (Min)	E (Max)	F (Nom)
MF-RG250	8.9	12.8	5.1±0.7	6.18	3.0	Φ 0.51
MF-RG300	7.1	11.0	5.1±0.7	7.6	3.0	Φ 0.81
MF-RG400	8.9	12.8	5.1±0.7	7.6	3.0	Φ 0.81
MF-RG500	10.4	14.3	5.1±0.7	7.6	3.0	Φ 0.81
MF-RG600	10.7	17.1	5.1±0.7	7.6	3.0	Φ 0.81
MF-RG700	11.2	19.7	5.1±0.7	7.6	3.0	Φ 0.81
MF-RG800	12.7	20.9	5.1±0.7	7.6	3.0	Φ 0.81
MF-RG900	14.0	21.7	5.1±0.7	7.6	3.0	Φ 0.81
MF-RG1000	16.5	25.2	5.1±0.7	7.6	3.0	Φ 0.81
MF-RG1100	17.5	26.0	5.1±0.7	7.6	3.0	Φ 0.81
MF-RG1200	17.5	28.0	10.2±0.7	7.6	3.5	Φ 1.0
MF-RG1400	23.5	27.9	10.2±0.7	7.6	3.5	Φ 1.0

This bulletin is intended to clarify the present product data and provide technical information for end user with design application. BOURNS Inc. reserves the right to change design or construction of any products, and also reserves the right to change or update any technical information contained in this bulletin.

This document shall not be reproduced or transferred to other documents or disclosed to others or used for any purpose other than that for which it was obtained without the express written consent of BOURNS Inc.

**Electrical performance:** (measured at 23 °C)

Part No.	I <sub>HOLD</sub>	I <sub>TRIP</sub>	P <sub>D TYP</sub>	Max. Time-To-Trip		R <sub>MIN</sub>	R <sub>MAX</sub>	R <sub>1 MAX</sub>
	(A)	(A)	(W)	(A)	(sec)	(Ω)	(Ω)	(Ω)
MF-RG250	2.5	4.7	1.0	12.5	5.0	0.0220	0.0350	0.0530
MF-RG300	3.0	5.1	2.3	15.0	1.0	0.0380	0.0645	0.0975
MF-RG400	4.0	6.8	2.4	20.0	1.7	0.0210	0.0385	0.0600
MF-RG500	5.0	8.5	2.6	25.0	2.0	0.0150	0.0230	0.0340
MF-RG600	6.0	10.2	2.8	30.0	3.3	0.0100	0.0185	0.0280
MF-RG700	7.0	11.9	3.0	35.0	3.5	0.0077	0.0130	0.0200
MF-RG800	8.0	13.6	3.0	40.0	5.0	0.0056	0.0110	0.0175
MF-RG900	9.0	15.3	3.3	45.0	5.5	0.0047	0.0092	0.0135
MF-RG1000	10.0	17	3.6	50.0	6.0	0.0040	0.0071	0.0102
MF-RG1100	11.0	18.7	3.7	55.0	7.0	0.0037	0.0062	0.0089
MF-RG1200	12.0	20.4	4.2	60.0	7.5	0.0033	0.0060	0.0086
MF-RG1400	14.0	23.8	4.6	70.0	9.0	0.0026	0.0045	0.0064

This bulletin is intended to clarify the present product data and provide technical information for end user with design application. BOURNS Inc. reserves the right to change design or construction of any products, and also reserves the right to change or update any technical information contained in this bulletin.  
This document shall not be reproduced or transferred to other documents or disclosed to others or used for any purpose other than that for which it was obtained without the express written consent of BOURNS Inc.