


**Isolating transducer
2-channel
IMX12-AI01-2I-2IU-H0/24VDC**



The 2-channel IMX12-AI01-2I-2IU-H0/24VDC HART® isolating transducer is designed to operate intrinsically safe HART® 2-wire transducers in the Ex area and to transmit the measured signals to the non-Ex area.

In addition to the analog signal also digital HART® communication signals can be transmitted bidirectionally. Furthermore, active and passive 2-wire HART® transmitters can be operated. The device is equipped with a 4 ... 20 mA input and output circuit (either as source or sink) or 1...5 V (source). The input signals are transmitted in the range of 3.8... 20.5 mA without interference 1:1 and made available at the outputs in the non-Ex area. Wire-break (< 3.5 mA) and short-circuit (> 22 mA) in the transducer circuit are output as current < 3.5 mA or voltage < 0.875 V.

A green LED indicates operational readiness. An error in the input circuit leads to a flashing red LED according to NE44.


The device can be used in safety circuits up to SIL2 (high and low demand according to IEC 61508) and meets the requirements of the NE21. It is equipped with removable screw terminals.

- ATEX, IECEx, NEPSI, INMETRO, Kosha, TR CU
- Installation in zone 2
- SIL 2
- Input circuits monitored for wire-break and short-circuit
- Complete galvanic isolation
- HART transparent
- Removable screw terminals

**Isolating transducer
2-channel
IMX12-AI01-2I-2IU-H0/24VDC**

Type designation	IMX12-AI01-2I-2IU-H0/24VDC
Ident no.	7580305
Nominal voltage	24 VDC
Operating voltage range	10...30 VDC
Power consumption	≤ 3.8 W
Transmitter connection	
Supply voltage	≥ 17 V / 20 mA
Input current	2 x 4...20 mA
Temperature drift supply voltage	≤ 0.03 %/K
Reference temperature	23 °C
Output circuits	
Output current	2 x Source/Sink (15...28V) 4...20 mA
Output voltage	2 x 1...5 V
Load resistance, current output	≤ 0.8 kΩ
Short-circuit	Output < 3.5 mA, if in the input circuit a current > 22 mA flows
Wire break	Output < 3.5 mA, if in the input circuit a current < 3.5 mA flows
Rise time (10...90 %)	≤ 5 ms
Fall time (90...10 %)	≤ 5 ms
Measuring accuracy	≤ 0.05 % of full scale
Reference temperature	23 °C
Temperature drift	≤ 0.002 % / K
Galvanic isolation	
Test voltage	2.5 kV
Input 1 to output 1	375 V peak value acc. to EN 60079-11
Input 2 to output 2	375 V peak value acc. to EN 60079-11
Input 1 to supply	375 V peak value acc. to EN 60079-11
Input 2 to supply	375 V peak value acc. to EN 60079-11
Output 1 to supply	50 V RMS acc. to EN 50178 and EN 61010-1
Output 2 to supply	50 V RMS acc. to EN 50178 and EN 61010-1
Output 1 to output 2	50 V RMS acc. to EN 50178 and EN 61010-1
Input 1 to input 2	60 V peak value acc. to EN 60079-11
Important note	For Ex-applications the values specified in the corresponding Ex certificates (ATEX, IECEx, UL, etc.) apply.
Ex approval acc. to conformity certificate	TÜV 15 ATEX 158337 X
Application area	II (1) G, II (1) D
ignition protection category	[Ex ia Ga] IIC; [Ex ia Da] IIIC
Application area	II 3 (1) G
Ignition protection type	Ex nA [ia Ga] IIC T4 Gc
Important note	If the device is used in applications to achieve functional safety according to IEC 61508, the safety manual must be used. Information in the data sheet are not valid for functional safety.
Use in SIL safety circuits	SIL 2 acc. to IEC 61508
Indication	
Operational readiness	green
Error indication	red

Dimensions



Isolating transducer
2-channel
IMX12-AI01-2I-2IU-H0/24VDC

Protection class	IP20																																																																																		
Flammability class acc. to UL 94	V-0																																																																																		
Ambient temperature	-25...+70 °C																																																																																		
Storage temperature	-40...+80 °C																																																																																		
Relative humidity	≤ 95 %																																																																																		
Dimensions	120 x 12.5 x 117 mm																																																																																		
Weight	183 g																																																																																		
Mounting instructions	DIN rail (NS35)																																																																																		
Housing material	Polycarbonate/ABS																																																																																		
Electrical connection	Removable screw clamp terminals, 2-pin																																																																																		
Terminal cross-section	0.2...2.5 mm ² (24 ... 13 AWG)																																																																																		
Tightening torque	0.5 Nm																																																																																		
Tightening torque	4.43 LBS-Inch																																																																																		
Environmental conditions	<table border="1"> <tr> <td>Operating altitude</td> <td>Up to 2000 m above sea level</td> </tr> <tr> <td>Pollution degree</td> <td>II</td> </tr> <tr> <td>Surge category</td> <td>II (EN 61010-1)</td> </tr> <tr> <td>Standards used</td> <td></td> </tr> <tr> <td>Voltage resistance and insulation</td> <td></td> </tr> <tr> <td></td> <td>EN 50178</td> </tr> <tr> <td></td> <td>EN 61010-1</td> </tr> <tr> <td></td> <td>EN 50155</td> </tr> <tr> <td></td> <td>GL VI-7-2</td> </tr> <tr> <td>Shock</td> <td></td> </tr> <tr> <td></td> <td>EN 61373 class B</td> </tr> <tr> <td></td> <td>EN 50155</td> </tr> <tr> <td></td> <td>GL VI-7-2</td> </tr> <tr> <td></td> <td>EN 60068-2-6</td> </tr> <tr> <td></td> <td>EN 60068-2-27</td> </tr> <tr> <td>Temperature</td> <td></td> </tr> <tr> <td></td> <td>EN 60068-2-1 Ad</td> </tr> <tr> <td></td> <td>EN 50155</td> </tr> <tr> <td></td> <td>GL VI-7-2</td> </tr> <tr> <td></td> <td>EN 60068-2-2 Bd</td> </tr> <tr> <td></td> <td>EN 60068-2-1</td> </tr> <tr> <td>Humidity</td> <td></td> </tr> <tr> <td></td> <td>EN 60068-2-38</td> </tr> <tr> <td>EMC</td> <td></td> </tr> <tr> <td></td> <td>EN 50155</td> </tr> <tr> <td></td> <td>GL VI-7-2</td> </tr> <tr> <td></td> <td>NE21</td> </tr> <tr> <td></td> <td>In the event of a conducted interference in the range of 150 kHz, the measuring error changes to ±700 µA</td> </tr> <tr> <td></td> <td>EN 61326-1</td> </tr> <tr> <td></td> <td>EN 61326-3-1</td> </tr> <tr> <td></td> <td>EN 61000-4-2</td> </tr> <tr> <td></td> <td>EN 61000-4-3</td> </tr> <tr> <td></td> <td>EN 61000-4-4</td> </tr> <tr> <td></td> <td>EN 61000-4-5</td> </tr> <tr> <td></td> <td>EN 61000-4-6</td> </tr> <tr> <td></td> <td>EN 61000-4-11</td> </tr> <tr> <td></td> <td>EN 61000-4-29</td> </tr> <tr> <td></td> <td>EN 55011</td> </tr> <tr> <td></td> <td>EN 55016</td> </tr> <tr> <td></td> <td>EN 50121-3-2</td> </tr> <tr> <td></td> <td>EN 61000-6-2</td> </tr> </table>	Operating altitude	Up to 2000 m above sea level	Pollution degree	II	Surge category	II (EN 61010-1)	Standards used		Voltage resistance and insulation			EN 50178		EN 61010-1		EN 50155		GL VI-7-2	Shock			EN 61373 class B		EN 50155		GL VI-7-2		EN 60068-2-6		EN 60068-2-27	Temperature			EN 60068-2-1 Ad		EN 50155		GL VI-7-2		EN 60068-2-2 Bd		EN 60068-2-1	Humidity			EN 60068-2-38	EMC			EN 50155		GL VI-7-2		NE21		In the event of a conducted interference in the range of 150 kHz, the measuring error changes to ±700 µA		EN 61326-1		EN 61326-3-1		EN 61000-4-2		EN 61000-4-3		EN 61000-4-4		EN 61000-4-5		EN 61000-4-6		EN 61000-4-11		EN 61000-4-29		EN 55011		EN 55016		EN 50121-3-2		EN 61000-6-2
Operating altitude	Up to 2000 m above sea level																																																																																		
Pollution degree	II																																																																																		
Surge category	II (EN 61010-1)																																																																																		
Standards used																																																																																			
Voltage resistance and insulation																																																																																			
	EN 50178																																																																																		
	EN 61010-1																																																																																		
	EN 50155																																																																																		
	GL VI-7-2																																																																																		
Shock																																																																																			
	EN 61373 class B																																																																																		
	EN 50155																																																																																		
	GL VI-7-2																																																																																		
	EN 60068-2-6																																																																																		
	EN 60068-2-27																																																																																		
Temperature																																																																																			
	EN 60068-2-1 Ad																																																																																		
	EN 50155																																																																																		
	GL VI-7-2																																																																																		
	EN 60068-2-2 Bd																																																																																		
	EN 60068-2-1																																																																																		
Humidity																																																																																			
	EN 60068-2-38																																																																																		
EMC																																																																																			
	EN 50155																																																																																		
	GL VI-7-2																																																																																		
	NE21																																																																																		
	In the event of a conducted interference in the range of 150 kHz, the measuring error changes to ±700 µA																																																																																		
	EN 61326-1																																																																																		
	EN 61326-3-1																																																																																		
	EN 61000-4-2																																																																																		
	EN 61000-4-3																																																																																		
	EN 61000-4-4																																																																																		
	EN 61000-4-5																																																																																		
	EN 61000-4-6																																																																																		
	EN 61000-4-11																																																																																		
	EN 61000-4-29																																																																																		
	EN 55011																																																																																		
	EN 55016																																																																																		
	EN 50121-3-2																																																																																		
	EN 61000-6-2																																																																																		