

High transmission ratio for easy cutting

and fatigue reducing operation

for strong gripping and pulling

With cutting edges for soft and hard wire

pressing performance

approx. 64 HRC

pliers thanks to optimised transmission ratio

Requires 50 % less effort compared with conventional combination

Pliers with tether attachment point for mounting a fall protection

Ergonomically optimised handle shape for firm contact to the hand

Additional gripping zone below the joint for powerful leverage and

Particularly effective cross-hatched knurled gripping zone in the jaws -

Cutting edges additionally induction-hardened, cutting edge hardness

Solid construction for heaviest strain; universally applicable

Vanadium electric steel, forged, multi stage oil-hardened

Product information

09 02 240 T

Lineman's Pliers

With tether attachment point American style

DIN ISO 5746 ASME B107.20



You Tube

Ge

General	
Article No.	09 02 240 T
EAN	4003773079941
Pliers	black atramentized
Head	polished
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
Weight	460 g
Dimensions	240 x 56 x 23 mm
Standard	DIN ISO 5746 ASME B107.20
Reach	no
RohS	no
Technical details	
Cutting capacities medium hard wire (diameter)	Ø 4.6 mm
Cutting capacities hard wire (diameter)	Ø 3.0 mm

•

•

•

•

•

•

•

system

Classification

Drop Protection System

olassification	
eCl@ss 5.1.4	21040301
ETIM 6.0	EC000836
proficl@ss 6.0	AAA967c005
UNSPSC 13.1	27112106

yes

technical change and errors excepted

KNIPEX Quality – Made in Germany





Gripping zone below the joint for powerful leverage

