



RCBO, 10 kA, 2P Type A, 30 mA, B-Char, In: 16A Un: 230V super-resistant

Model	
product brand name	SENTRON
product designation	RCBO
design of the product	Super resistant K
General technical data	
number of poles	2
number of poles with protection	2
design of pole	2P
tripping characteristic class	B
mechanical service life (operating cycles) typical	10 000
overvoltage category	III
degree of pollution	3
Voltage	
type of voltage of the operating voltage	AC
insulation voltage (Ui) rated value	500 V
surge voltage resistance rated value	4 000 V
surge current resistance at (8/20) μ s	3 kA
Supply voltage	
supply voltage	
• at AC rated value	230/240 V
• for testing equipment minimum	195 V
operating frequency	50/60 Hz
supply voltage frequency rated value	50 Hz
Protection class	
protection class IP	IP20, if the distribution board is installed, with connected conductors
Switching capacity	
short-circuit current breaking capacity (Icn) according to EN 61009-1 rated value	10 kA
switching capacity current	
• according to EN 60898 rated value	10 kA
• according to IEC 60947-2 rated value	15 kA
rated residual switching capacity (I Δ m) according to IEC 61009-1	4.5 kA
energy limitation class	3
Dissipation	
power loss [W]	
• for rated value of the current at AC in hot operating state per pole	1.14 W
• maximum	2.3 W
operational current	
• at 30 °C rated value	16 A

• at 40 °C rated value	15.2 A
• at 45 °C rated value	14.8 A
• at 50 °C rated value	14.3 A
• at 55 °C rated value	13.9 A
• at 60 °C rated value	13.4 A
• at 70 °C rated value	12.5 A

Product details

product feature	
• halogen-free	No

Connections

connectable conductor cross-section solid	
• minimum	1 mm ²
• maximum	35 mm ²
connectable conductor cross-section stranded	
• minimum	1 mm ²
• maximum	35 mm ²
connectable conductor cross-section finely stranded with core end processing	
• minimum	1 mm ²
• maximum	35 mm ²
tightening torque with screw-type terminals	
• minimum	2 N·m
• maximum	2 N·m
position of power supply cord	Either top or bottom

Mechanical Design

height	85 mm
width	36 mm
depth	72 mm
installation depth	70 mm
number of modular width units	2
mounting position	any
net weight	235 g
weight with packaging	265 g

Environmental conditions

influence of the surrounding temperature	Max. 95% humidity
ambient temperature during operation	
• minimum	-25 °C
• maximum	40 °C
ambient temperature during storage	
• minimum	-40 °C
• maximum	70 °C
number of test cycles for environmental testing according to IEC 60068-2-30	28

General Product Approval

Declaration of Conformity

other

[Confirmation](#)

[Miscellaneous](#)



[Confirmation](#)

other

Dangerous Good

Environment

[Miscellaneous](#)

[Miscellaneous](#)

[Transport Information](#)

[Environmental Confirmations](#)

Further information

Siemens has decided to exit the Russian market (see here).
<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an

EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SU1324-6FR16>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SU1324-6FR16>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SU1324-6FR16

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

5/23/2023

