

Vishav

Lead (Pb)-free Commodity Thick Film Chip Resistors



FEATURES

· High volume product suitable for commercial applications RoHS



- Pure tin solder contacts on Ni barrier layer COMPLIANT HALOGEN provides compatibility with lead (Pb)-free and FREE lead containing soldering processes
- Metal glaze on high guality ceramic
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912

STANDAR	STANDARD ELECTRICAL SPECIFICATIONS									
MODEL	CASE SIZE INCH	CASE SIZE METRIC	POWER RATING P ₇₀ W	LIMITING ELEMENT VOLTAGE U _{max.} AC _{RMS} /DC V	TEMPERATURE COEFFICIENT ppm/K	TOLERANCE %	RESISTANCE RANGE Ω	SERIES		
					± 200	± 0.5	10.0 to 10M	E96		
		RR 0603M	0.05	30	-200 / +400	± 0.5	1.0 to 9.76	L90		
					± 100	± 1	47.0 to 1M	E24; E96 E24		
	0201				± 200		10.0 to 10M			
CRCW0201	0201				-200 / +400		1.0 to 9.76			
					± 200	. F	10.0 to 10M			
					-200 / +400	± 5	1.0 to 9.1			
Zero-Ohm-Resistor: $R_{max.} = 50 \text{ m}\Omega$, $I_{max.}$ at 70 °C = 1.0 A										

Notes

Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material.

TECHNICAL SPECIFICATIONS					
PARAMETER	UNIT	CRCW0201			
Rated Dissipation at 70 °C ⁽¹⁾	W	0.05			
Operating Voltage Umax. ACRMS/DC	V	30			
Insulation Voltage U _{ins} (1 min)	V	50			
Insulation Resistance	Ω	> 10 ⁹			
Operating Temperature Range	°C	-55 to +155			
Weight	mg	0.17			

Note

⁽¹⁾ The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature of 155 °C is not exceeded.


Revision:	31-Mar-16	6
-----------	-----------	---

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.

www.vishay.com


ISHAY

Vishay



PACKAGING							
MODEL	CODE	QUANTITY	CARRIER TAPE	WIDTH	PITCH	REEL DIAMETER	
	ED = ET7	10 000	Paper tape acc. to IEC 60068-3 Type I		2 mm	180 mm/7"	
CRCW0201	EI = ET2	20 000		8 mm		254 mm/10"	
	EE = EF4	50 000				330 mm/13"	

DIMENSIONS in millimeters



SI	ZE	DIMENSIONS					SOLDER PAD DIMENSIONS		
INCH	METRIC	L	w	н	T1	T2	а	b	Ι
0201	0603	0.6 ± 0.05	0.3 ± 0.05	0.23 ± 0.05	0.15 ± 0.05	0.10 ± 0.05	0.28	0.43	0.23


Note

• No marking for 0201 size.



Vishay

DERATING



TEST PROCEDURES AND REQUIREMENTS							
EN 60115-1	IEC 60068-2		PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (∆R)			
CLAUSE	TEST	TEST	Stability for product types:				
	METHOD		CRCW0201 e3	1 Ω to 10 M Ω			
4.5	-	Resistance	-	± 0.5 %; ± 1 %; ± 5 %			
4.7	-	Voltage proof	$U = 1.4 \text{ x } U_{\text{ins}}; 60 \text{ s}$	No flashover or breakdown			
4.13	58 (Td)	Solderability	Solder bath method; Sn60Pb40 non activated flux; $(235 \pm 5) \ ^{\circ}C$ $(2 \pm 0.2) \ ^{\circ}S$	Good tinning (≥ 95 % covered) no visible damage			
4.13	56 (10)	Solderability	Solder bath method; Sn96.5Ag3Cu0.5 non-activated flux; $(245 \pm 5) \ ^{\circ}C$ $(3 \pm 0.3) \ ^{\circ}S$	Good tinning (≥ 95 % covered) no visible damage			
4.8.4.2	-	Temperature coefficient	(20 / -55 / 20) °C and (20 / 125 / 20) °C	± 100 ppm/K, ± 200 ppm/K, -200 ppm/K / +400 ppm/K			
4.32	21 (Uu ₃)	Shear (adhesion)	9 N	No visible damage			
4.33	21 (Uu ₁)	Substrate bending	Depth 2 mm; 3 times	No visible damage, no open circuit in bent position $\pm (0.5 \% R + 0.05 \Omega)$			
4.40		Rapid change	30 min. at -55 °C; 30 min. at 125 °C				
4.19	14 (Na)	of temperature	5 cycles	± (0.5 % <i>R</i> + 0.05 Ω)			
			1000 cycles	± (1 % <i>R</i> + 0.05 Ω)			
4.23	-	Climatic sequence:	-				
4.23.2	2 (Ba)	Dry heat	125 °C; 16 h				
4.23.3	30 (Db)	Damp heat, cyclic	55 °C; \geq 90 % RH; 24 h; 1 cycle				
4.23.4	1 (Aa)	Cold	-55 °C; 2 h	± (2 % <i>R</i> + 0.1 Ω)			
4.23.5	13 (M)	Low air pressure	1 kPa; (25 ± 10) °C; 1 h				
4.23.6	30 (Db)	Damp heat, cyclic	55 °C; \geq 90 % RH; 24 h; 5 cycles				
4.23.7	- DC load		$U = \sqrt{P_{70} \times R} \le U_{\text{max.}}$				



Vishay

TEST PROCEDURES AND REQUIREMENTS								
EN 60115-1	IEC 60068-2	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (\Delta R)				
CLAUSE	TEST		Stability for product types:					
	METHOD		CRCW0201 e3	1 Ω to 10 M Ω				
4.05.4		Endurance at 70 °C	$U = \sqrt{P_{70} \times R} \le U_{\text{max.}};$ 1.5 h on; 0.5 h off;					
4.25.1	-		70 °C; 1000 h	± (2 % <i>R</i> + 0.1 Ω)				
			70 °C; 8000 h	± (4 % <i>R</i> + 0.1 Ω)				
4.18.2	58 (Td)	Resistance to soldering heat	Solder bath method (260 \pm 5) °C; (10 \pm 1) s	± (1 % <i>R</i> + 0.05 Ω)				
4.35	-	Flamability, needle flame test	IEC 60695-11-5; 10 s	No burning after 30 s				
4.24	78 (Cab)	Damp heat, steady state	(40 ± 2) °C; (93 ± 3) % RH; 56 days	± (2 % <i>R</i> + 0.1 Ω)				
4.25.3	-	Endurance at upper category temperature	155 °C, 1000 h	\pm (2 % R + 0.1 Ω)				
4.29	45 (XA)	Component solvent resistance	Isopropyl alcohol; 50 °C; method 2	No visible damage				
4.22	6 (Fc)	Vibration, endurance by sweeping	$ \begin{array}{l} f=10 \ Hz \ to \ 2000 \ Hz; \\ x, y, z \leq 1.5 \ mm; \\ A \leq 200 \ m/s^2; \\ 10 \ sweeps \ per \ axis \end{array} $	± (0.5 % <i>R</i> + 0.05 Ω)				

All tests are carried out in accordance with the following specifications:

- EN 60115-1, generic specification
- EN 140400, sectional specification
- EN 140401-802, detail specification
- IEC 60068-2-x, environmental test procedures

Packaging of components is done in paper tapes according to IEC 60286-3.

4



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.