H100 HARNESS

1036293 AND 1036294

The H100 series is the Honeywell cost-effective, quality, construction and general industry compliant harness designed to meet the most common fall protection needs.

The Miller H100 series has been designed around a simple concept; provide a fundamental fall protection line with exceptional value. The new Miller H100 series was assembled to meet the most common fall protection needs while maintaining a focus on value and safety.



FEATURES AND BENEFITS



Honeywell Miller branded: built with our legendary quality and reliability



Lightweight: more comfortable



Covered identification labels: protects labels during the life of the harness



New distinctive vibrant color webbing



Cost effective




H100 HARNESS


MATERIALS

Webbing	1-3/4 in. Polyester				
Keepers	Elastic				
Thread	Polyester				
D-Ring*	Galvanized steel				
Steel Buckles*	Galvanized steel				
Label Pack	Evoprene, Nylon				
Label Materials	PVC				

^{*} All hardware meets ASTM (50) fifty-hour salt spray test requirements.

H100 HARNESS FEATURES







ORDERING INFORMATION

SKU	LEG	CHEST	D-RINGS / OTHER				SPECIAL FEATURES	WEIGHT	COUNTRY OF	
NUMBER	BUCKLES	BUCKLES	BACK	CHEST	HIPS	SHOULDER ADJUSTERS			ORIGIN	
1036293	Mating	Mating	Steel	N/A	N/A	N/A	Sub-pelvic strap and lanyard keepers	0.8 Kg	China	
1036294	Mating	Mating	Steel	front webbing loops	N/A	N/A	Sub-pelvic strap and lanyard keepers	0.9 Kg	China	

Meets applicable EN 361-2002, REACH Model. UKCA Pending

PACKAGING

12 Units

United Kingdom Honeywell Safety Products (UK) Limited Edison Rd - Basingstoke RG21 6QD United Kingdom

Phone: +44 (0) 1256 693200 Fax: +44 (0) 1256 693 300 **info-uk.hsp@honeywell.com**

information sp@honeywell.com

HIS Fall H100 11110022 Harness DTS_ENa | 01/2020 © 2020 Honeywell International Inc.

THE FUTURE IS WHAT WE MAKE IT

