

Indexable insert countersink, twin-blade

for universal use up to 1300 N/mm² with CC..06 and CC..09..

ATORN[®]

Application

180° countersinks with CC.. indexable inserts in the diameter range from 10.00–33.00 mm, in the material groups steel, stainless steel, non-ferrous metals, cast materials and special alloys for use in single part and series production.

Version

- backing material made from high-grade steel with clamping surface in line with DIN 1835B

Advantage

- precision-engineered insert seat and two blades ensure optimum machining results and smooth running even under difficult operating conditions
- universal use in all material groups
- cost-efficient tool in comparison with mono-block solutions



Art. No.	11243 160
Number of cutting edges	2 PCS
Coolant supply	Internal
Tool holding device	HB parallel shank
Cutting edge diameter	16 mm
Cantilever length	30 mm
Length	92 mm
Min. pilot hole diameter	5 mm
Shaft diameter	12 mm
Suitable for indexable inserts	CC..06

EAN-Code

4050293112405