



Figure similar

POWER SUPPLY; PHASES:1; PN(KW):0,12;
 UPRI(V):400-230(240)-115(120); USEC(V DC):24;
 ISEC(A DC):5/6 (60/40 CEL); F(HZ):50...60; VECTOR
 GR./SHIELD WNG.:II0 /0; PROTECTION CL.:I;
 TA/ISOKL:60 /B; W(%):5; IP00; TYPE OF
 TERMINALS:SCREW/TAB CONNECTION;
 INSTALLATION:MOUNTING RAILS; EN 61558-2-6,
 EN61131-2 >SAFETY ISOLATING TRANSFORMER<

General technical data:

Product designation		4AV2201-2EB00-0B
product brand name		SIDAC
Vector group		II0
Certificate of suitability		CE / cRUus
Product function		
<ul style="list-style-type: none"> • Temperature monitoring 		No
<ul style="list-style-type: none"> • Insulation monitoring 		No
<ul style="list-style-type: none"> • Short-circuit and overload proof 		No
<ul style="list-style-type: none"> • varistor protective wiring 		Yes
Operating resource protection class		I
Number of shielding windings		0

Inputs:

Phase number of the inputs		1
Type of current of the inputs		AC
Input voltage		
<ul style="list-style-type: none"> • _1 Rated value 	V	400
<ul style="list-style-type: none"> • _2 Rated value 	V	230
<ul style="list-style-type: none"> • _3 Rated value 	V	115
Electrical input frequency		
<ul style="list-style-type: none"> • minimum 	Hz	50
<ul style="list-style-type: none"> • maximum 	Hz	60
Input voltage		
<ul style="list-style-type: none"> • minimum 	V	103.5

• maximum	V	424
Input current		
• _1 Rated value	A	0.56
• _2 Rated value	A	0.97
• _3 Rated value	A	1.94
Type of electrical connection at input for main current circuit		screw-type terminals / tab terminals

Outputs:

Type of current		
• _1 at output		DC
Output voltage		
• _1 Rated value	V	24
Output voltage of the measurement signal at analog output for DC maximum	V	28.8
Output voltage of the measurement signal at analog output for DC minimum	V	20.4
Output current		
• _1 Rated value	A	5
Type of electrical connection at output for main current circuit		screw-type terminals / tab terminals
Relative residual ripple		
• of the output voltage 1 for main current circuit maximum	%	5

Ambient conditions:

Thermal class acc. to IEC 60085		B
Ambient temperature Rated value	°C	60
Protection class IP		IP00

Mechanical data:

Mounting type		standard rail
Construction form of the iron core		EI 105/60
Width	m	105
Height	m	157
Depth	m	113

Certificates/ approvals:

General Product Approval	Shipping Approval	other
---------------------------------	--------------------------	--------------



[Declaration of Conformity](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=4AV22012EB000B>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AV22012EB000B>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=4AV22012EB000B&lang=en

last modified:

16.03.2015