

## **Features**

Voltage Range : 3.6V to 51V Double slug type construction

# **Mechanical Data**

Case	: Glass case Minimelf DL-35
Terminals	: Solder plated, solderable per MIL-STD-750, Method 2026
Polarity	: Colour band denotes cathode end
Mounting position	: Any
Weight	: 0.05 gram Approx

#### **Maximum Ratings And Electrical Characteristics**

Rating at 25°C ambient temperature unless otherwise specified. Single phase, half wave ,60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

Characteristic	Symbol	Value	Unit	
Power Dissipation at Tamb = 25°C	Ptot	500*	mW	
Junction Temperature	Tj	175	°C	
Storage Temperature Range	Tstg	-55 to +175	°C	
Thermal Resistance Junction to Ambient Air	Reja	0.3	k/mW (Max.)	
Forward Voltage Typ at IF = 100mA	VF	1	Volts (Max.)	

\* Valid Provided that leads are kept at ambient temperature at a distance of 8mm from case


Notes: Suffix "B" indicates Zener Voltage Tolerance 5%

# **Specification Table**


Part Number	Nominal Zener Voltage	Zener Test Current	Max. 2	Zener Impedance	Coefficient		Max. Reverse Leakage Current	
	Vz@Izt	lzτ	Zzt@lzt	Zzт@lzк(*)=0.25mA	Temperature	IR	@Vr	Izм
1N5231B+	5.1	20	17	1600	±0.03	5	2	89
1N5232B+	5.6	20	11	1600	+0.038	5	3	81
1N5234B+	6.2	20	7	1000	+0.045	5	4	73
1N5236B+	7.5	20	6	500	+0.058	3	6	61
1N5240B+	10	20	17	600	+0.075	3	8	45
1N5242B +	12	20	30	600	+0.077	1	9.1	38
1N5245B+	15	8.5	16	600	+0.082	0.1	11	30

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro





### **Dimensions:**



**Dimensions : Millimetres** 

### **Part Number Table**

Description	Part Number		
Zener Diode, 5.1V DO-35 500mW	1N5231B+		
Zener Diode, 5.6V DO-35 500mW	1N5232B+		
Zener Diode, 6.2V DO-35 500mW	1N5234B+		
Zener Diode, 7.5V DO-35 500mW	1N5236B+		
Zener Diode, 10V DO-35 500mW	1N5240B+		
Zener Diode, 12V DO-35 500mW	1N5242B +		
Zener Diode, 15V DO-35 500mW	1N5245B+		

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness. any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

