

Shockproof dial gauges

Application:

For measuring lengths and length differences, e.g. concentricity, flatness, positional measurements.

Execution:

- Measuring pin and clamping shaft made from durable stainless steel

Advantage:

- Impacts against the gauge slide are not transferred to the measuring mechanism; in this way, display accuracy is maintained for a long time.

Delivery:

In a case



Art. no.	33003 010
Brand	HK
Manufacturer Part Number	33003010
Length measuring range	3 mm
Scale value	0.01 mm
Measurement travel of one pointer revolution	0.5 mm
Outer diameter	40 mm
Shock protection	Yes
Material of outer ring	Metal
Measurement force	1 N
DIN	878
Calibration Group	CE
Gross Weight	0.120 kg
Product Group	331

EAN

4039247206957