ZB5AW333

Illuminated push button head, plastic, flush, green, Ø22, spring return, plain lens integral LED





Main

Range of product	Harmony XB5
Product or component type	Head for illuminated push-button
Device short name	ZB5
Product compatibility	Integral LED
Bezel material	Dark grey plastic
Mounting diameter	0.87 in (22 mm)
Sale per indivisible quantity	1
Head type	Standard
Shape of signaling unit head	Round
Type of operator	Spring return
Operator profile	Green flush, unmarked
Operator additional information	With plain lens

Complementary

CAD overall width	1.14 in (29 mm)
CAD overall height	1.14 in (29 mm)
CAD overall depth	1.18 in (30 mm)
Net Weight	0.04 lb(US) (0.017 kg)
Resistance to high pressure washer	7000000 Pa at 55 °C, distance : 0.1 m
Mechanical durability	10000000 cycles
Main group	Illum push-button
Group of product	Flush push integral LED
Station name	XALD 15 cut-outs XALK 25 cut-outs
Cap/operator or lens colour	Green
Marking	Unmarked
Electrical composition code	M1 6 single front mounting integral LED M2 6 single and double front mounting integral LED M6 2 single front mounting integral LED and transformer M10 2 single front mounting integral LED MF1 2 single front mounting integral LED MR1 2 single rear mounting integral LED
Device presentation	Basic sub-assemblies

Environment

Protective treatment	TC	
Ambient air temperature for storage	-40158 °F (-4070 °C)	
Ambient air temperature for operation	-40158 °F (-4070 °C)	
Overvoltage category	Class II conforming to IEC 60536	
IP degree of protection	IP66 conforming to IEC 60529 IP67 IP69 IP69K	
NEMA degree of protection	NEMA 13 NEMA 4X	

IK degree of protection	IK05 EN 50102	
Standards	EN/IEC 60947-5-4	
	JIS C8201-5-1	
	GB 14048.5	
	UL 508	
	EN/IEC 60947-1	
	EN/IEC 60947-5-1	
	CSA C22.2 No 14	
	JIS C8201-1	
Product certifications	GL	
	DNV	
	LROS (Lloyds register of shipping)	
	RINA	
	BV	
	CSA	
	UL Listed	
Vibration resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27	
	50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27	

Ordering and shipping details

ordering directions	
Category	22467 - PUSHBUTTONS,22MM(PLASTIC) NEW
Discount Schedule	CS2
GTIN	00785901374640
Nbr. of units in pkg.	1
Package weight(Lbs)	0.03 lb(US) (0.01 kg)
Returnability	Yes
Country of origin	FR

Packing Units

3	
Unit Type of Package 1	PCE
Package 1 Height	1.34 in (3.4 cm)
Package 1 width	1.77 in (4.5 cm)
Package 1 Length	2.13 in (5.4 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	2.40 lb(US) (1.09 kg)
Package 2 Height	1.34 in (3.4 cm)
Package 2 width	1.77 in (4.5 cm)
Package 2 Length	10.43 in (26.5 cm)
Unit Type of Package 3	S03
Number of Units in Package 3	300
Package 3 Weight	12.41 lb(US) (5.628 kg)
Package 3 Height	11.81 in (30 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

Green Premium product	
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	
☑ REACh Declaration	
Yes	
Pro-active compliance (Product out of EU RoHS legal scope) EVEL RoHS Declaration	
Yes	

RoHS exemption information	₽¥Yes	
China RoHS Regulation	China RoHS Declaration	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End Of Life Information	
Contractual warranty		
Warranty	18 months	