

## Twist drill type N HSS, steam-treated

for universal use up to 1000 N/mm<sup>2</sup>

**ORION**<sup>®</sup>

### Application:

Standard geometry for universal use up to 1000 N/mm<sup>2</sup>.

### Execution:

- Twist drill with universal standard geometry

### Advantage:

- excellent all-round properties and precise cutting pattern
- universal use: minimises tool costs and improves flexibility
- Steam treatment ensures favourable adherence of coolant



<b>Art. no.</b>	<b>11071 350</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	11071350
<b>Cutting material</b>	HSS
<b>Surface</b>	Vaporised
<b>Type</b>	N
<b>Angle of the tip</b>	118 Degree
<b>DIN</b>	345
<b>Tool holding device</b>	Morse taper shank
<b>Cutting edge diameter</b>	33 mm
<b>Chip flute length</b>	185 mm
<b>Length</b>	334 mm
<b>Morse taper size</b>	MK 4
<b>f steel 700</b>	0.38 mm/r
<b>Gross Weight</b>	1.328 kg
<b>Product Group</b>	1AP

### EAN

4039247023233